



VTM[™] Current Multiplier VTM48MP010×107AA1

Sine Amplitude Converter[™] (SAC[™])

Features & Benefits

- 45.6V_{DC} to 0.95V_{DC} 107A current multiplier
 - Operating from standard 48V or 24V PRM[™] regulators
 - Up to 60 Volts DC input
 - K of 1/48 provides up to 107A DC output current
- High efficiency (>94%) reduces system power consumption
- High density (1119A/in³)
- Vicor's 1323 ChiP package enables low impedance interconnect to system board
- Provides enable / disable control, internal temperature monitoring, internal current monitoring
- ZVS / ZCS resonant Sine Amplitude Converter topology
- Parallel up to 10 modules

Typical Applications

- Computing and Telecom Systems
 - Optimized for the Intel VR12.0 Processor Specification
- Automated Test Equipment
- High Density Power Supplies
- Communications Systems

Product Ratings		
$V_{IN} = 0$ to 60V	I _{OUT} = 107A (nom)	
$V_{OUT} = 0$ to 1.25V (no load)	K = 1/48	

Product Description


The Vicor's 1323 ChiP VTM current multiplier is a high efficiency (>94%) Sine Amplitude ConverterTM (SACTM) operating from a 0 to $60V_{DC}$ primary bus to deliver a 0 to $1.25V_{DC}$ low voltage output. The Sine Amplitude Converter offers a low AC impedance beyond the bandwidth of most downstream regulators; therefore capacitance normally at the load can be located at the input to the Sine Amplitude Converter. Since the K factor of the VTM48MP010x107AA1 is 1/48, the capacitance value can be reduced by a factor of 2304, resulting in savings of board area, materials and total system cost.

The VTM48MP010x107AA1 is provided in Vicor's 1323 ChiP package compatible with standard pick-and-place assembly processes. The co-molded ChiP package provides enhanced thermal management due to a large thermal interface area and superior thermal conductivity. The high conversion efficiency of the VTM48MP010x107AA1 increases overall system efficiency and lowers operating costs compared to conventional approaches.

The VTM48MP010x107AA1 enables the utilization of Factorized Power Architecture[™] which provides efficiency and size benefits by lowering conversion and distribution losses and promoting high density point of load conversion.



Pin Configuration



Pin Numbering and Descriptions

Pin Number	Signal Name	Туре	Function
A1, A2 C1, C2 E1, E2	+OUT	OUTPUT POWER	Positive output terminal
B1, B2 D1, D2 F1, F2	-OUT	OUTPUT POWER RETURN	Negative output terminal
G1	EN	INPUT	To disable VTM in system
G2	ТМ	OUTPUT	Temperature monitor and Power Good Flag
H1	VCC	INPUT	Power train controller supply
H2	CM	OUTPUT	Current monitor
11	+IN	INPUT POWER	Positive input terminal
12	-IN	INPUT POWER RETURN	Negative input terminal



Vicor's comprehensive line of power solutions includes high density AC-DC and DC-DC modules and accessory components, fully configurable AC-DC and DC-DC power supplies, and complete custom power systems.

Information furnished by Vicor is believed to be accurate and reliable. However, no responsibility is assumed by Vicor for its use. Vicor makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication. Vicor reserves the right to make changes to any products, specifications, and product descriptions at any time without notice. Information published by Vicor has been checked and is believed to be accurate at the time it was printed; however, Vicor assumes no responsibility for inaccuracies. Testing and other quality controls are used to the extent Vicor deems necessary to support Vicor's product warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

Specifications are subject to change without notice.

Visit http://www.vicorpower.com/dc-dc/non-isolated-regulated/data-center-prm-and-vtm for the latest product information.

Vicor's Standard Terms and Conditions and Product Warranty

All sales are subject to Vicor's Standard Terms and Conditions of Sale, and Product Warranty which are available on Vicor's webpage (<u>http://www.vicorpower.com/termsconditionswarranty</u>) or upon request.

Life Support Policy

VICOR'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS PRIOR WRITTEN APPROVAL OF THE CHIEF EXECUTIVE OFFICER AND GENERAL COUNSEL OF VICOR CORPORATION. As used herein, life support devices or systems are devices which (a) are intended for surgical implant into the body, or (b) support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in a significant injury to the user. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system or to affect its safety or effectiveness. Per Vicor Terms and Conditions of Sale, the user of Vicor products and components in life support applications assumes all risks of such use and indemnifies Vicor against all liability and damages.

Intellectual Property Notice

Vicor and its subsidiaries own Intellectual Property (including issued U.S. and Foreign Patents and pending patent applications) relating to the products described in this data sheet. No license, whether express, implied, or arising by estoppel or otherwise, to any intellectual property rights is granted by this document. Interested parties should contact Vicor's Intellectual Property Department.

The products described on this data sheet are protected by the following U.S. Patents Numbers:

5,945,130; 6,403,009; 6,710,257; 6,911,848; 6,930,893; 6,934,166; 6,940,013; 6,969,909; 7,038,917; 7,145,186; 7,166,898; 7,187,263; 7,202,646; 7,361,844; D496,906; D505,114; D506,438; D509,472; and for use under 6,975,098 and 6,984,965.

Contact Us: http://www.vicorpower.com/contact-us

Vicor Corporation

25 Frontage Road Andover, MA, USA 01810 Tel: 800-735-6200 Fax: 978-475-6715 www.vicorpower.com

email

Customer Service: <u>custserv@vicorpower.com</u> Technical Support: <u>apps@vicorpower.com</u>

©2017 Vicor Corporation. All rights reserved. The Vicor name is a registered trademark of Vicor Corporation. All other trademarks, product names, logos and brands are property of their respective owners.

Rev 1.5 07/2017

