

DE 3 - 502351

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE CERTIFICATS D'ESSAIS DES EQUIPEMENTS ELECTRIQUES (IECEE) METHODE OC

## CB TEST CERTIFICATE CERTIFICAT D'ESSAI OC

Product

Power supply DC-DC Converter

Name and address of the applicant

Vicor Corporation 25 Frontage Road Andover MA 01810, USA

Name and address of the manufacturer

Vicor Corporation

25 Frontage Road, Andover MA 01810, USA

Name and address of the factory

Vicor Inc.

400 Federal Street, Andover MA 01810, USA

Ratings and principal characteristics

Rated Input Voltage:

50 V DC

Rated Output Power: Rated Output Voltage: 320 W Max 13 V DC

Trade mark (if any)

DC-DC Converter

Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model/type Ref.

DCM3414V50M13C2T09 (3414 VIA DCM Series)

(see certificate attachment for model matrix, license conditions and rating information)

Additional information (if necessary)

Certificate DE 3 – 502000 issued 2016-07-29 is replaced by this version due to technical changes

A sample of the product was tested and found to be in conformity with

IEC 60950-1:2005

IEC 60950-1:2005/AMD1:2009 IEC 60950-1:2005/AMD2:2013

as shown in the Test Report Ref. No. which forms part of this certificate

72106922-100

This CB Test Certificate is issued by the National Certification Body Ce Certificat d'essai OC est établi par l'Organisme National de Certification

Date,

2017-04-18

CB 17 04 21433 517

Willing Storm

William Stinson

TÜV SÜD Product Service GmbH · Certification Body · Ridlerstrasse 65 · D-80339 München



**Product Service** 



## Attachment to Certificate CB 17 04 21433 517

VIA DCM Model Number Matrix: DCMaaaabccdwwxxyzz

Example: DCM3414V50M13C2T09

DCM = Constant

00111	Conclain
Produc	t Function
DCM	DC-DC Converter Module

aaaa = 3414

ge Size (Length x Width)
3.4 in x 1.4 in

b = V

Packa	ige Type	
V	Chassis mount	
В	Board mount	

cc = 50

Max Ir	nput Voltage	
50	50 Vdc	
75	75 Vdc	

d = M

	Ratio (Vi		
Α	1.10	G	1.95
В	1.21	Н	2.14
С	1.33	J	2.36
D	1.46	K	2.59
E	1.61	L	2.85
F	1.77	M	3.14

ww = 13

VV VV — 1	J .		
Maximu	um Output Voltage rounded to the	nearest	Volt (Vout nominal + 10% trim),
any 2 d	igits from 00 to 60, non-inclusive I	ist of exa	imples below
04	3.6 Vdc (3.3 Vdc + 10%)	26	26.4 Vdc (24.0 Vdc + 10%)
06	5.5 Vdc (5.0 Vdc + 10%)	31	30.8 Vdc (28.0 Vdc + 10%)
13	13.2 Vdc (12.0 Vdc + 10%)	40	39.6 Vdc (36.0 Vdc + 10%)
17	16.5 Vdc (15.0 Vdc + 10%)	53	52.8 Vdc (48.0 Vdc + 10%)

xx = C2

<b>Maximur</b>	n Output Pow	er	
A6	160 W	C2	320 W
A8	180 W		

y = T

Product Grade				
С	-20 to 100°C	T	-40 to 100°C	
M	-55 to 100°C	S	-55 to 100°C	

Test Report No: 72106922-100

Date, 2017-04-18

CB 17 04 2143 517

Willing Horn



Product Service

TÜV SÜD Product Service GmbH • Certification Body • Ridlerstrasse 65 • D-80339 München



## Attachment to Certificate CB 17 04 21433 517

VIA DCM Model Number Matrix: DCMaaaabccdwwxxyzz

Example: DCM3414V50M13C2T09 (cont.)

zz = 09

Options (no	on-safety rela	ited), any alphanum	eric, non-incl	usive list	
Option ID	Pin length	Communication	Option ID	Pin length	Communication
01		Analog	07	Short	Remote control
02		Digital PMBus	09	Long	Analog
03		Remote control	10	Long	Digital PMBus
05	Short	Analog	11	Long	Remote control
06	Short	Digital PMBus			

## License Conditions:

The VIA DCM3414 series of DC-DC converters is designed for building-in.

Conditions of Acceptability – When installed in the end use equipment, the following are among considerations to be made:

- 1. The VIA output is separated from the input by basic insulation
- 2. The input is intended to be a TNV-2 or other non-hazardous secondary circuit, the output is considered SELV
- 3. See de-rating curves for maximum output power vs. case temperature
- 4. The VIA DCM's were evaluated with external fuse rated 30A. EATON (Cooper/Bussmann) ABC series or Littelfuse Nano2 series
- 5. Outputs above 240W are considered to be at a hazardous energy level

Test Report No: 72106922-100

Date, 2017-04-18

CB 17 04 2143 517

Milling flow



Product Service

TÜV SÜD Product Service GmbH • Certification Body • Ridlerstrasse 65 • D-80339 München