



Ref. Certif. No.

DE 3 - 501617

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE CERTIFICATS D'ESSAIS DES EQUIPEMENTS ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE CERTIFICAT D'ESSAI OC

Product
Produit

Power supply
AC-DC Configurable Power Supply

Name and address of the applicant
Nom et adresse du demandeur

Vicor Corporation
25 Frontage Road
Andover MA 01810, USA

Name and address of the manufacturer
Nom et adresse du fabricant

Vicor Corporation
25 Frontage Road, Andover MA 01810, USA

Name and address of the factory
Nom et adresse de l'usine

Vicor Inc.
400 Federal Street, Andover MA 01810, USA

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

Rated Input Voltage: 115/230 V AC
Rated Frequency: 47-63 Hz or 47-440 Hz
Rated Input Current: 15 A max.
See certificate attachment for additional ratings

Trade mark (if any)
Marque de fabrique (si elle existe)

Vicor

Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais constructeur

CTF Stage 3

Model/type Ref.
Ref. de type

VP-abbbbbbcd (VIPAC)
See certificate attachment for nomenclature breakdown and ratings.

Additional information (if necessary)
Information complémentaire (si nécessaire)

Certificate DE 3 – 59986 issued 2012-11-29 is replaced by this version due to technical changes

A sample of the product was tested and found to be in conformity with
Un échantillon de ce produit a été essayé et a été considéré conforme à la

IEC 60950-1(ed.2);am1;am2

as shown in the Test Report Ref. No. which forms part of this certificate
comme indiqué dans le Rapport d'essais numéro de référence qui constitue une partie de ce certificat

DI1209255-100

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**

Date, 2015-12-03
CB 15 12 21433 471

William Stinson



TÜV SÜD Product Service GmbH · Certification Body · Ridlerstrasse 65 · D-80339 München

Product Service

Attachment to Certificate CB 15 12 21433 471

VIPAC Family Tree Model Number VP-abbbbbcd

VP = Constant, defines AC input ratings

115/230 Vac, 15 A Max, 47-63 Hz or 47-440Hz

a = DC-DC converter configuration		Max Output Voltage	Output Power Max
A	3 Micro size dc-dc converters	48 Vdc	450 W
B	2 Mini size dc-dc converters	48 Vdc	500 W
C	2 Maxi size dc-dc converters	48 Vdc	900 W
D	2 Micro size dc-dc converters	48 Vdc	300 W
E	1 Mini size dc-dc converter	48 Vdc	250 W
F	1 Maxi size dc-dc converter	48 Vdc	500 W
G	1 Micro size dc-dc converter	48 Vdc	150 W

bbbbbb =	0-9, sequential assigned number, represents customer configuration
c =	0-9, represents model number error check (non-safety related)
d =	Optional Suffix, E represents RoHS compliance (non-safety related)

Test Report No: DI1209255-100

Date, 2015-12-03
CB 15 12 21433 471




Product Service

TÜV SÜD Product Service GmbH • Certification Body • Ridlerstrasse 65 • D-80339 München