

ConverterPAC Description

ConverterPACs are the family of slide-in output assemblies used in MegaPAC power supplies. There are currently 12 ConverterPACs available for use. Most ConverterPACs of the same length are interchangeable within a MegaPAC and between different AC input MegaPAC chassis. They can be added, moved, or changed as necessary. The type of ConverterPAC used in this slot is a JuniorQPAC.

JuniorQPAC (LJ = Non-RoHS; GLJ = RoHS)

The JuniorQPAC output assembly consists of a **VI-J00** DC to DC converter that converts the high voltage bus to the desired regulated output voltage. JuniorQPACs can provide up to 100 Watts of output power (cannot be paralleled) and are fused with a single PC-Tron, DC-rated, fast-acting fuse. A passive LC filter is used to reduce output ripple/noise down to 1% typical, and 2% maximum peak-to-peak from 10% to 100% of rated load. Ripple and common mode noise filters on the output reduce ripple under any load conditions to 10mV p-p or 0.15% whichever is greater. An **optional** DC Power Good signal or output voltage Trim potentiometer can be specified. The JuniorQPAC contains output overcurrent protection, which recovers automatically when the overcurrent condition is removed.



Overvoltage protection and overtemperature limiting are not available. Newer JuniorQPACs have Autosense. This feature automatically locally senses the output if remote sense is not used. To check if an output has the Autosense feature, measure the impedance from the + Out to + Sense and - Out to - Sense pins. If the impedance is 5 ohms, then the output has Autosense and does not require local sense jumpers. If a unit does not have Autosense, sense connections must be made. Please also note that newer JuniorQPACs have new outputs studs that are 1/8" longer to allow for multiple lugs. They are fully compatible with the original flanged nut ConverterPACs. JuniorQPACs can only be used in the extended length MegaPACs. For further technical information about ConverterPACs, contact Applications Engineering at 1-800-927-9474.

Options Available for JuniorQPAC

OPTIONS


D	Power Good
T	Trim +/-10%
F*	Trim: +10%/-50%

AVAILABILITY

OPTIONAL
OPTIONAL
OPTIONAL

* Note: Not available for 1st Gen 10V, 12V and 15V modules. For more details, contact Factory.

JuniorQPAC Output and Connector Pin Identification



J2 REMOTE SENSE TRIM/SC & POWER GOOD

MATING HDWR:
HOUSING- MOLEX P/N: 50-37-5073
TERMINALS- MOLEX P/N: 08-70-1040
CRIMP TOOL MOLEX P/N: 63811-5200

7	+SENSE
6	-SENSE
5	TRIM
4	Vcc IN
3	POWER GOOD
2	POWER GOOD INVERTED
1	SIGNAL GROUND

Output connector kits (optional) for your MegaPAC supply are available for purchase from Westcor:

	Part Number
Single phase input	43075
Three phase input	43541