



# DCM<sup>™</sup> DC-DC Converter DCM4623xD2K26E0y7z



 $P_{OUT} = 500 W$ 

I<sub>OUT</sub> = 20.84 A

# Isolated, Regulated DC Converter

**Product Ratings** 

The DCM Isolated, Regulated DC Converter is a DC-DC

unregulated power sources to the point-of-load.

converter, operating from an unregulated, wide range input to

generate an isolated 24.0 Vdc output. With its high frequency zero voltage switching (ZVS) topology, the DCM converter

Modular DCM converters and downstream DC-DC products

Leveraging the thermal and density benefits of Vicor's ChiP

management options with very low top and bottom side

thermal impedances. Thermally-adept ChiP based power

weight and efficiency attributes, quickly and predictably.

consistently delivers high efficiency across the input line range.

support efficient power distribution, providing superior power system performance and connectivity from a variety of

packaging technology, the DCM module offers flexible thermal

components enable customers to achieve cost effective power system solutions with previously unattainable system size,

 $V_{IN} = 160 \text{ V to } 420 \text{ V}$ 

V<sub>OUT</sub> = 24.0 V

(14.4 V to 26.4 V Trim)

**Product Description** 

### **Features & Benefits**

- Isolated, regulated DC-DC converter
- Up to 500 W, 20.84 A continuous
- 92.7% peak efficiency
- 1040 W/in<sup>3</sup> Power density •
- Wide input range 160 420 Vdc
- Safety Extra Low Voltage (SELV) 24.0 V Nominal Output •
- 4242 Vdc isolation
- ZVS high frequency switching
- Enables low-profile, high-density filtering
- Fully operational current limit
- OV, OC, UV, short circuit and thermal protection
- Military Standard Compliance
  - MIL-STD-810G
  - MIL-STD-202G
  - MIL-STD-704E/F<sup>[a]</sup>
  - MIL-STD-461E/F/G<sup>[b]</sup> MIL-STD-1275E <sup>[b] [c]</sup>
- 4623 through-hole ChiP package
  - 1.886" x 0.898" x 0.284"
    - (47.91 mm x 22.8 mm x 7.21 mm)

## **Typical Applications**

- Industrial
- Process Control •
- Transportation / Heavy Equipment

**Part Ordering Information** 

• Defense / Aerospace

<sup>[a]</sup> DC power characteristics only.

<sup>[b]</sup> For applications requiring compliance to MIL-STD-461 or 1275,


please contact Vicor Applications Engineering.

<sup>[c]</sup> Applicable only for 16 – 50V<sub>IN</sub> range designs.


Product Function		kage ize	Package Type	Max Input Voltage	Range Ratio	Max Output Voltage	Max Output Power	Temperature Grade	Option
DCM	46	23	х	D2	K	26	EO	У	7z
DCM = DC-DC Converter	Length in mm x 10	Width in mm x 10	T = Through hole ChiPs		Internal F	Reference	<u></u>	T = -40°C – 125°C M = -55°C – 125°C	70 = Enhanced V <sub>OUT</sub> Regulation / Analog Control Interface Version



# **Typical Application**



Typical Application 1: Single DCM4623xD2K26E0y7z, to a non-isolated regulator, and direct to load




Typical Application 2: Single DCM4623xD2K26E0y7z with common- and differential-mode input filters

**Rev 1.3** 11/2020



VICO

# **Pin Configuration**



# **Pin Descriptions**

Pin Number	Signal Name	Туре	Function
A1	+IN	INPUT POWER	Positive input power terminal
B1	TR	INPUT	Enables and disables trim functionality. Adjusts output voltage when trim active.
C1	EN	INPUT	Enables and disables power supply
D1	FT	OUTPUT	Fault monitoring
E1	-IN	INPUT POWER RETURN	Negative input power terminal
A'2, C'2	+OUT	OUTPUT POWER	Positive output power terminal
B'2, D'2	-OUT	OUTPUT POWER RETURN	Negative output power terminal

# **Absolute Maximum Ratings**

The absolute maximum ratings below are stress ratings only. Operation at or beyond these maximum ratings can cause permanent damage to the device. Electrical specifications do not apply when operating beyond rated operating conditions.

Parameter	Comments	Min	Мах	Unit
Input Voltage (+IN to –IN)		-0.5	460.0	V
Input Voltage Slew Rate		-1	1	V/µs
TR to - IN		-0.3	3.5	V
EN to -IN		-0.3	3.5	V
		-0.3	3.5	V
FT to -IN			5	mA
Output Voltage (+Out to –Out)		-0.5	31.2	V
Dielectric withstand (input to output)	Reinforced insulation	4242		Vdc
	T Grade	-40	125	°C
Internal Operating Temperature	M Grade	-55	125	°C
Champer Transform	T Grade	-40	125	°C
Storage Temperature	M Grade	-65	125	°C
Average Output Current			24.3	А





Figure 1 — Thermal Specified Operating Area: Max Output Power vs. Case Temp, module at minimum full load efficiency



VICC

Figure 2 — Electrical Specified Operating Area

# **Electrical Specifications**

Specifications apply over all line, trim and load conditions, internal temperature  $T_{INT} = 25^{\circ}$ C, unless otherwise noted. **Boldface** specifications apply over the temperature range of -40°C <  $T_{INT}$  < 125°C for T grade and -55°C <  $T_{INT}$  < 125°C for M grade.

Attribute	Symbol	Conditions / Notes	Min	Тур	Мах	Unit
		Power Input Specifications				
Input voltage range	V <sub>IN</sub>	Continuous operation	160	270	420	V
Inrush current (peak)	I <sub>INRP</sub>	With maximum C <sub>OUTEXT</sub> , full resistive load			8.0	A
Input capacitance (internal)	C <sub>IN-INT</sub>	Effective value at nominal input voltage		0.8		μF
Input capacitance (internal) ESR	R <sub>CIN-INT</sub>	At 1 MHz		2.50		mΩ
Input inductance (external)	L <sub>IN</sub>	Differential mode, with no further line bypassing			5	μΗ
		No Load Specifications				
Input power – disabled	PQ	Nominal line, see Fig. 3		1.1	2.0	W
nput power – disabled	ΤQ	Worst case line, see Fig. 3			3.4	W
pout power apphed with pollood	D	Nominal line, see Fig. 4		4.9	9.4	W
nput power – enabled with no load	P <sub>NL</sub>	Worst case line, see Fig. 4			10.5	W
		Power Output Specifications				
Output voltage set point	V <sub>OUT-NOM</sub>	At $V_{\text{IN}}$ = 270V, nominal trim at 100% load, $T_{\text{INT}}$ = 25°C	23.88	24.0	24.12	V
Rated output voltage trim range	V <sub>OUT-TRIMMING</sub>	Trim range over temp, with > 20% rated load. Specifies the Low, Nominal and High Trim conditions.	14.4	24.0	26.4	V
		At nominal line, nominal trim, full load and ambient temperature	-0.5		0.5	
Output voltage regulation	%V <sub>OUT</sub>	At nominal line, nominal trim and: • Load >20% of full load and ambient temperature • Full load and over temperature	-1.0		1.0	%
		All other conditions (does not include light load regulation)	-2.5		2.5	
Output voltage accuracy	%V <sub>OUTACCURACY</sub>	The total output voltage set-point accuracy from the calculated V <sub>OUT</sub> based on load, temp and trim. Excludes: • $\Delta V_{OUTLL}$	-3.0		3.0	%
Output voltage light load regulation	ΔV <sub>OUT-LL</sub>	<ul> <li>%V<sub>OUTREGULATION</sub></li> <li>0% to 20% load, additional V<sub>OUT</sub> relative to V<sub>OUT</sub> accuracy; see Design Guidelines section</li> </ul>	-0.00		2.40	V
Rated output power	Роит	Continuous, $V_{OUT} \ge 24.0 V$	500			W
Rated output current	lout	Continuous, $V_{OUT} \le 24.0 \text{ V}$	20.84			А
Output current limit	I <sub>OUT-LM</sub>	Of rated I <sub>OUT</sub> max. Fully operational current limit, for nominal trim and below	100	120	141	%
Current limit delay	t <sub>IOUT-LIM</sub>	The module will power limit in a fast transient event		1		ms
		Full load, nominal line, nominal trim	91.7	92.7		%
Efficiency	η	Full load, over line and temperature, nominal trim	90.1			%
,		50% load, over rated line, temperature and trim	88.3			%
Output voltage ripple	V <sub>OUT-PP</sub>	20 MHz bandwidth. At nominal trim, minimum C <sub>OUTEXT</sub> and at least 20 % rated load		753		mV
Output capacitance (internal)	COUT-INT	Effective value at nominal output voltage		42		μF
Output capacitance (internal) ESR	R <sub>COUT-INT</sub>	At 1 MHz		0.069		mΩ
Output capacitance (external)	Coutext	Excludes component temperature coefficient For load transients that remain > 20% rated load	220	0.000	2200	μF
Output capacitance (external)	Coutexttrans	Excludes component temperature coefficient For load transients down to 0% rated load, with static trim	220		2200	μF
Output capacitance (external)	C <sub>OUT-EXT-</sub>	Excludes component temperature coefficient For load transients down to 0% rated load, with dynamic trimming	220		2200	μF
	TRANS-TRIM					



# **Electrical Specifications (cont.)**

Specifications apply over all line, trim and load conditions, internal temperature  $T_{INT} = 25^{\circ}C$ , unless otherwise noted. **Boldface** specifications apply over the temperature range of  $-40^{\circ}C < T_{INT} < 125^{\circ}C$  for T grade and  $-55^{\circ}C < T_{INT} < 125^{\circ}C$  for M grade.

Attribute	Symbol	Conditions / Notes	Min	Тур	Max	Unit
		Power Output Specifications (Cont.)				
Initialization dolay	+	Power Output Specifications (Cont.)		25	40	mc
Initialization delay	t <sub>INIT</sub>	See state diagram From rising edge EN, with V <sub>IN</sub> pre-applied. See timing		25	40	ms
Output turn-on delay	t <sub>ON</sub>	diagram		200		μs
Output turn-off delay	t <sub>OFF</sub>	From falling edge EN. See timing diagram			600	μs
Soft start ramp time	t <sub>ss</sub>	At full rated resistive load, with min $C_{OUT-EXT}$		23		ms
Output voltage threshold for max rated load current	V <sub>OUT-FL</sub> -THRESH	During startup, V <sub>OUT</sub> must achieve this threshold before output can support full rated current			12.0	V
Output current at startup	I <sub>OUT-START</sub>	Max load current at startup while $V_{OUT}$ is below $V_{OUTFL_THRESH}$	2.08			А
Monotonic soft-start threshold voltage	V <sub>OUT-MONOTONIC</sub>	Output voltage rise becomes monotonic with 10% of preload once it crosses $V_{\mbox{OUT-MONOTONIC}}$			12.0	V
Minimum required disabled duration	t <sub>OFF-MIN</sub>	This refers to the minimum time a module needs to be in the disabled state before it will attempt to start via EN			2	ms
Minimum required disabled duration for predictable restart	t <sub>off-monotonic</sub>	This refers to the minimum time a module needs to be in the disabled state before it is guaranteed to exhibit monotonic soft-start and have predictable startup timing			100	ms
Voltage deviation (transient)	%V <sub>OUT-TRANS</sub>			<10		%
Settling time	t <sub>settle</sub>	Minimum $C_{OUT\_EXT}$ (10 $\leftrightarrow$ 90% load step).		16.0		ms
		Powertrain Protections				
Input Voltage Initialization threshold	V <sub>IN-INIT</sub>	Threshold to start t <sub>INIT</sub> delay			75	V
Input Voltage Reset threshold	V <sub>IN-RESET</sub>	Latching faults will clear once $V_{\text{IN}}$ falls below $V_{\text{IN-RESET}}$	50			V
Input undervoltage lockout threshold	VIN-UVLO-		96.00		152.00	V
Input undervoltage recovery threshold	V <sub>IN-UVLO+</sub>	See Timing diagram			160.00	V
Input overvoltage lockout threshold	V <sub>IN-OVLO+</sub>				455	V
Input overvoltage recovery threshold	VIN-OVLO-	See Timing diagram	420			V
Output overvoltage threshold	V <sub>OUT-OVP</sub>	From 25% to 100% load. Latched shutdown	30.00			V
Output overvoltage threshold	V <sub>OUT-OVP-LL</sub>	From 0% to 25% load. Latched shutdown	31.20			V
Minimum current limited V <sub>OUT</sub>	V <sub>OUT-UVP</sub>	Over all operating steady-state line and trim conditions			8.98	V
Overtemperature threshold (internal)	T <sub>INT-OTP</sub>		125			°C
Power limit	P <sub>LIM</sub>				1100	W
V <sub>IN</sub> overvoltage to cessation of powertrain switching	t <sub>ovlo-sw</sub>	Independent of fault logic		1.0		μs
V <sub>IN</sub> overvoltage response time	t <sub>ovlo</sub>	For fault logic only			200	μs
V <sub>IN</sub> undervoltage response time	t <sub>UVLO</sub>				100	ms
Short circuit response time	t <sub>SC</sub>	Powertrain on, operational state			200	μs
Short circuit, or temperature fault recovery time	t <sub>FAULT</sub>	See Timing diagram		1		S



# **Signal Specifications**

Specifications apply over all line, trim and load conditions, internal temperature  $T_{INT} = 25^{\circ}$ C, unless otherwise noted. **Boldface** specifications apply over the temperature range of -40°C <  $T_{INT}$  < 125°C for T grade and -55°C <  $T_{INT}$  < 125°C for M grade.

	Enable: EN									
• The EN pin enal	oles and disables	s the DCM converter; when h	neld low the uni	t will be disabled.						
• The EN pin has	an internal pull-	up to VCC and is referenced	to the -IN pin o	f the converter.						
SIGNAL TYPE	STATE	ATTRIBUTE	SYMBOL	<b>CONDITIONS / NOTES</b>	MIN	NOM	MAX	UNIT		
		EN enable threshold	V <sub>ENABLE-EN</sub>				2.31	V		
DIGITAL		EN disable threshold	V <sub>ENABLE-DIS</sub>		0.99			V		
INPUT	Any	Internally generated $V_{CC}$	V <sub>CC</sub>		3.21	3.30	3.39	V		
		EN internal pull up resistance to V <sub>CC</sub>	R <sub>ENABLE-INT</sub>		9.9	10.0	10.1	kΩ		

#### Trim: TR

• The TR pin enables and disables trim functionality when V<sub>IN</sub> is initially applied to the DCM converter. When Vin first crosses V<sub>IN-UVLO+</sub>, the voltage on TR determines whether or not trim is active.

• If TR is not floating at power up and has a voltage less than TR trim enable threshold, trim is active.

• If trim is active, the TR pin provides dynamic trim control with at least 30Hz of -3dB control bandwidth over the output voltage of the DCM converter.

 $\bullet$  The TR pin has an internal pull-up to V\_{CC} and is referenced to the -IN pin of the converter.

SIGNAL TYPE	STATE	ATTRIBUTE	SYMBOL	CONDITIONS / NOTES	MIN	NOM	MAX	UNIT
DIGITAL		TR trim disable threshold	V <sub>TRIM-DIS</sub>	Trim disabled when TR above this threshold at power up			3.20	V
INPUT	Startup	TR trim enable threshold	V <sub>TRIM-EN</sub>	Trim enabled when TR below this threshold at power up	3.15			V
		Internally generated $V_{\text{CC}}$	V <sub>CC</sub>		3.21	3.30	3.39	V
	Operational	TR pin functional range	V <sub>TRIM-RANGE</sub>		0.00	2.46	3.16	V
ANALOG INPUT	with Trim enabled	V <sub>OUT</sub> referred TR pin resolution	V <sub>OUT-RES</sub>	With $V_{CC} = 3.3 V$		45		mV
		TR internal pull up resistance to V <sub>CC</sub>	R <sub>TRIM-INT</sub>		9.9	10.0	10.1	kΩ

#### Fault: FT

• The FT pin is a Fault flag pin.

• When the module is enabled and no fault is present, the FT pin does not have current drive capability.

• Whenever the powertrain stops (due to a fault protection or disabling the module by pulling EN low), the FT pin output Vcc and provides current to drive an external ciruit.

• When module starts up, the FT pin is pulled high to V<sub>CC</sub> during microcontroller initialization and will remain high until soft start process starts.


SIGNAL TYPE	STATE	ATTRIBUTE	SYMBOL	CONDITIONS / NOTES	MIN	NOM	MAX	UNIT
	Any	FT internal pull up resistance to V <sub>CC</sub>	R <sub>FAULT-INT</sub>		494	499	504	kΩ
DIGITAL		FT voltage	V <sub>FAULT-ACTIVE</sub>	At rated current drive capability	3.0			V
OUTPUT	FT Active	FT current drive capability	I <sub>FAULT-ACTIVE</sub>	Over-load beyond the ABSOLUTE MAXIMUM ratings may cause module damage	4			mA
		FT response time	t <sub>FT-ACTIVE</sub>	Delay from cessation of switching to FT Pin Active			200	μs



/ICC

### **High Level Functional State Diagram**


Conditions that cause state transitions are shown along arrows. Sub-sequence activities listed inside the state bubbles.



Rev 1.3

# **Timing Diagrams**


Module Inputs are shown in blue; Module Outputs are shown in brown.





# **Timing Diagrams (Cont.)**

Module Inputs are shown in blue; Module Outputs are shown in brown.





### **Typical Performance Characteristics**

The following figures present typical performance at  $T_C = 25^{\circ}C$ , unless otherwise noted. See associated figures for general trend data.




Figure 3 — Disabled power dissipation vs.  $V_{IN}$ 




Figure 4 — No load power dissipation vs. V<sub>IN</sub>, at nominal trim




Figure 5 — Ideal V<sub>OUT</sub> vs. load current, at 25°C case




Figure 6 — Full Load Efficiency vs. V<sub>IN</sub>, at low trim




Figure 7 — Full Load Efficiency vs. V<sub>IN</sub>, at nominal trim




Figure 8 — Full Load Efficiency vs.  $V_{IN}$ , at high trim



### **Typical Performance Characteristics (cont.)**

The following figures present typical performance at  $T_c = 25^{\circ}C$ , unless otherwise noted. See associated figures for general trend data.





Figure 9 — Efficiency and power dissipation vs.load at  $T_{CASE} = -40^{\circ}C$ , nominal trim



**Figure 10** — Efficiency and power dissipation vs.load at  $T_{CASE} = 25$  °C, nominal trim




Figure 11 — Efficiency and power dissipation vs.load at  $T_{CASE} = 90^{\circ}C$ , nominal trim




Figure 12 — Nominal powertrain switching frequency vs. load, at nominal trim




Figure 13 — Effective internal input capacitance vs. applied voltage




Figure 14 — Startup from EN,  $V_{IN}$  = 270 V,  $C_{OUT\_EXT}$  = 2200 µF,  $R_{LOAD}$  = 1.152  $\Omega$ 



# **Typical Performance Characteristics (cont.)**

The following figures present typical performance at  $T_c = 25^{\circ}C$ , unless otherwise noted. See associated figures for general trend data.




Figure 15 — Nominal powertrain switching frequency vs. load, at nominal  $V_{\rm IN}$ 




Figure 16 — Output voltage ripple,  $V_{IN}$  = 270 V,  $V_{OUT}$  = 24.0 V,  $C_{OUT\_EXT}$  = 220 µF,  $R_{LOAD}$  = 1.152  $\Omega$ 



### **General Characteristics**

Specifications apply over all line, trim and load conditions, internal temperature  $T_{INT} = 25^{\circ}C$ , unless otherwise noted. **Boldface** specifications apply over the temperature range of  $-40^{\circ}C < T_{INT} < 125^{\circ}C$  for T grade and  $-55^{\circ}C < T_{INT} < 125^{\circ}C$  for M grade.

Attribute	Symbol	Conditions / Notes	Min	Тур	Мах	Unit
		Mechanical				
Length	L		47.53/[1.871]	47.91/[1.886]	48.29/[1.901]	mm/[in]
Width	W		22.67/[0.893]	22.8/[0.898]	22.93/[0.903]	mm/[in]
Height	Н		7.11/[0.28]	7.21/[0.284]	7.31/[0.288]	mm/[in]
Volume	Vol	No heat sink		7.93/[0.48]		cm <sup>3</sup> /[in <sup>3</sup>
Weight	W			29.2/[1.03]		g/[oz]
		Nickel	0.51		2.03	
Lead finish		Palladium	0.02		0.15	μm
		Gold	0.003		0.051	
		Thermal				
	_	T-Grade	-40		125	°C
Operating internal temperature	T <sub>INT</sub>	M-Grade	-55		125	°C
Thermal resistance top side	$\theta_{\text{INT-TOP}}$	Estimated thermal resistance to maximum temperature internal component from isothermal top		1.60		°C/W
Thermal resistance leads	$\theta_{\text{INT-LEADS}}$	Estimated thermal resistance to maximum temperature internal component from isothermal leads		5.90		°C/W
Thermal resistance bottom side	θ <sub>INT-BOTTOM</sub>	Estimated thermal resistance to maximum temperature internal component from isothermal bottom		1.80		°C/W
Thermal capacity				21.5		Ws/°C
		Assembly				
	_	T-Grade	-40		125	°C
Storage temperature	T <sub>ST</sub>	M-Grade	-65		125	°C
ESD rating	HBM	Method per Human Body Model Test ESDA/JEDEC JDS-001-2012	CLASS 1C			V
-	CDM	Charged Device Model JESD22-C101E	CLASS 2			
		Soldering <sup>[1]</sup>				
Peak temperature top case		For further information, please contact factory applications			135	°C

<sup>[1]</sup> Product is not intended for reflow solder attach.



## **General Characteristics (Cont.)**

Specifications apply over all line, trim and load conditions, internal temperature  $T_{INT} = 25^{\circ}$ C, unless otherwise noted. **Boldface** specifications apply over the temperature range of -40°C <  $T_{INT}$  < 125°C for T grade and -55°C <  $T_{INT}$  < 125°C for M grade.

Attribute	Symbol	Conditions / Notes	Min	Тур	Max	Unit	
		Safety					
		IN to OUT	4242			Vdc	
Dielectric Withstand Test	V <sub>HIPOT</sub>	IN to CASE	2121			Vdc	
		OUT to CASE	2121			Vdc	
		Reliability					
MTBF		MIL-HDBK-217 FN2 Parts Count 25°C Ground Benign, Stationary, Indoors / Computer		1.85		MHrs	
		Telcordia Issue 2, Method I Case 3, 25°C, 100% D.C., GB, GC		3.68		MHrs	
		Agency Approvals					
		cTÜVus, EN 60950-1					
Agency approvals/standards		cURus, UL 60950-1					
		CE Marked for Low Voltage Directive and RoHS Recast Directive, as applicable					



### **Pin Functions**

#### +IN, -IN

Input power pins. -IN is the reference for all control pins, and therefore a Kelvin connection for the control signals is recommended as close as possible to the pin on the package, to reduce effects of voltage drop due to -IN currents.

#### +OUT, -OUT

Output power pins.

#### EN (Enable)

This pin enables and disables the DCM converter; when held low the unit will be disabled. It is referenced to the -IN pin of the converter. The EN pin has an internal pull-up to  $V_{CC}$  through a 10 k $\Omega$  resistor.

- Output enable: When EN is allowed to pull up above the enable threshold, the module will be enabled. If leaving EN floating, it is pulled up to V<sub>CC</sub> and the module will be enabled.
- Output disable: EN may be pulled down externally in order to disable the module.
- EN is an input only, it does not pull low in the event of a fault.

#### TR (Trim)

The TR pin is used to select the trim mode and to trim the output voltage of the DCM converter. The TR pin has an internal pull-up to  $V_{CC}$  through a 10.0 k $\Omega$  resistor.

The DCM will latch trim behavior at application of  $V_{\rm IN}$  (once  $V_{\rm IN}$  exceeds  $V_{\rm IN-UVLO+}),$  and persist in that same behavior until loss of input voltage.

- At application of V<sub>IN</sub>, if TR is sampled at above V<sub>TRIM-DIS</sub>, the module will latch in a non-trim mode, and will ignore the TR input for as long as V<sub>IN</sub> is present.
- At application of V<sub>IN</sub>, if TR is sampled at below V<sub>TRIM-EN</sub>, the TR will serve as an input to control the real time output voltage. It will persist in this behavior until V<sub>IN</sub> is no longer present.

If trim is active when the DCM is operating, the TR pin provides dynamic trim control at a typical 30 Hz of -3dB bandwidth over the output voltage. TR also decreases the current limit threshold when trimming above  $V_{OUT-NOM}$ .

#### FT (Fault)


The FT pin provides a Fault signal.

Anytime the module is enabled and has not recognized a fault, the FT pin is inactive. FT has an internal 499 k $\Omega$  pull-up to Vcc, therefore a shunt resistor, R<sub>SHUNT</sub> of approximately 50 k $\Omega$  can be used to ensure the LED is completly off when there is no fault, per the diagram below.

Whenever the powertrain stops (due to a fault protection or disabling the module by pulling EN low), the FT pin becomes active and provides current to drive an external circuit.

When active, FT pin drives to V<sub>CC</sub>, with up to 4 mA of external loading. Module may be damaged from an over-current FT drive, thus a resistor in series for current limiting is recommended.

The FT pin becomes active momentarily when the module starts up.



# Typical External Circuits for Signal Pins (TR, EN, FT)

### **Design Guidelines**

#### **Building Blocks and System Design**

The DCM<sup>™</sup> converter input accepts the full 160 to 420 V range, and it generates an isolated trimmable 24.0 Vdc output.

The DCM converter provides a tightly regulated output voltage; please refer to the Output Voltage Load Regulation specification in the Electrical Specifications table.

The DCM4623xD2K26E0y7z is designed to be used in applications where the output power requirements are up to 500 W.

#### Soft Start

When the DCM starts, it will go through a soft start. The soft start routine ramps the output voltage by modulating the internal error amplifier reference. This causes the output voltage to approximate a piecewise linear ramp. The output ramp finishes when the voltage reaches either the nominal output voltage, or the trimmed output voltage in cases where trim mode is active.

During soft-start, the maximum load current capability is reduced. Until Vout achieves at least  $V_{OUT-FL-THRESH}$ , the output current must be less than  $I_{OUT-START}$  in order to guarantee startup. Note that this is current available to the load, above that which is required to charge the output capacitor.

#### Trim Mode and Output Trim Control

When the input voltage is initially applied to a DCM, and after  $t_{INIT}$  elapses, the trim pin voltage  $V_{TR}$  is sampled. The TR pin has an internal pull up resistor to  $V_{CC}$ , so unless external circuitry pulls the pin voltage lower, it will pull up to  $V_{CC}$ . If the initially sampled trim pin voltage is higher than  $V_{TRIM-DIS}$ , then the DCM will disable trimming as long as the  $V_{IN}$  remains applied. In this case, for all subsequent operation the output voltage will be programmed to the nominal. This minimizes the support components required for applications that only require the nominal rated Vout, and also provides the best output setpoint accuracy, as there are no additional errors from external trim components.

If at initial application of  $V_{IN}$ , the TR pin voltage is prevented from exceeding  $V_{TRIM-EN}$ , then the DCM will activate trim mode, and it will remain active for as long as  $V_{IN}$  is applied.

V<sub>OUT</sub> set point can be calculated using the equation below:

$$V_{OUT-FL} = 9.9773 + (18.7794 \bullet V_{TR}/V_{CC}) \tag{1}$$

Or using the online tool, DCM Trim Calculator, find the value of  $V_{TR}$  or trim resistor to set the desired  $V_{OUT}$ : http://www.vicorpower.com/calculators

Note that the trim mode is not changed when a DCM recovers from any fault condition or being disabled.

Module performance is guaranteed through output voltage trim range  $V_{OUT-TRIMMING}$ . If  $V_{OUT}$  is trimmed above this range, then certain combinations of line and load transient conditions may trigger the output OVP.

#### **Overall Output Voltage Transfer Function**

Taking trim (equation 1) into account, the general equation relating the DC  $V_{OUT}$  to programmed trim (when active), load is given by:

$$V_{OUT} = 9.9773 + (18.7794 \cdot V_{TR}/V_{CC}) + \Delta V_{OUT-LL} \quad (2)$$

Finally, note that when the load current is below 20% of the rated capacity, there is an additional  $\Delta V$  which may add to the output voltage, depending on the line voltage which is related to light load boosting. Please see the section on light load boosting below for details.

Use 0 V for  $\Delta V_{OUT-LL}$  when load is above 20% of rated load. See section on light load boosting operation for light load effects on output voltage.

#### **Output Current Limit**

The DCM features a fully operational current limit which effectively keeps the module operating inside the Safe Operating Area (SOA) for all valid trim and load profiles. The current limit approximates a "brick wall" limit, where the output current is prevented from exceeding the current limit threshold by reducing the output voltage via the internal error amplifier reference. The current limit threshold at nominal trim and below is typically 120% of rated output current, but it can vary between 100% to 141%. In order to preserve the SOA, when the converter is trimmed above the nominal output voltage, the current limit threshold is automatically reduced to limit the available output power.

When the output current exceeds the current limit threshold, current limit action is held off by 1ms, which permits the DCM to momentarily deliver higher peak output currents to the load. Peak output power during this time is still constrained by the internal Power Limit of the module. The fast Power Limit and relatively slow Current Limit work together to keep the module inside the SOA. Delaying entry into current limit also permits the DCM to minimize droop voltage for load steps.

Sustained operation in current limit is permitted, and no derating of output power is required.

Some applications may benefit from well matched current distribution, in which case fine tuning sharing via the trim pins permits control over sharing. The DCM does not require this for proper operation, due to the power limit and current limit behaviors described here.

Current limit can reduce the output voltage to as little as the UVP threshold ( $V_{OUT-UVP}$ ). Below this minimum output voltage compliance level, further loading will cause the module to shut down due to the output undervoltage fault protection.

#### Line Impedance, Input Slew rate and Input Stability Requirements

Connect a high-quality, low-noise power supply to the +IN and –IN terminals. Additional capacitance may have to be added between +IN and –IN to make up for impedances in the interconnect cables as well as deficiencies in the source.

Excessive source impedance can bring about system stability issues for a regulated DC-DC converter, and must either be avoided or compensated by filtering components. A 1  $\mu$ F input capacitor is the minimum recommended in case the source impedance is insufficient to satisfy stability requirements.

Additional information can be found in the filter design application note:

www.vicorpower.com/documents/application\_notes/vichip\_appnote23.pdf

Please refer to this input filter design tool to ensure input stability: <u>http://app2.vicorpower.com/filterDesign/intiFilter.do</u>.

Ensure that the input voltage slew rate is less than 1V/us, otherwise a pre-charge circuit is required for the DCM input to control the input voltage slew rate and prevent overstress to input stage components.



#### Input Fuse Selection

The DCM is not internally fused in order to provide flexibility in configuring power systems. Input line fusing is recommended at the system level, in order to provide thermal protection in case of catastrophic failure. The fuse shall be selected by closely matching system requirements with the following characteristics:

- Current rating (usually greater than the DCM converter's maximum current)
- Maximum voltage rating (usually greater than the maximum possible input voltage)
- Ambient temperature
- Breaking capacity per application requirements
- Nominal melting I<sup>2</sup>t
- Recommended fuse: See Agency Approvals for Recommended Fuse <u>http://www.vicorpower.com/dc-dc/isolated-</u> regulated/dcm#Documentation

#### **Fault Handling**

#### Input Undervoltage Fault Protection (UVLO)

The converter's input voltage is monitored to detect an input under voltage condition. If the converter is not already running, then it will ignore enable commands until the input voltage is greater than  $V_{IN-UVLO+}$ . If the converter is running and the input voltage falls below  $V_{IN-UVLO-}$ , the converter recognizes a fault condition, the powertrain stops switching, and the output voltage of the unit falls.

Input voltage transients which fall below UVLO for less than  $t_{\rm UVLO}$  may not be detected by the fault proection logic, in which case the converter will continue regular operation. No protection is required in this case.

Once the UVLO fault is detected by the fault protection logic, the converter shuts down and waits for the input voltage to rise above  $V_{IN-UVLO+}$ . Provided the converter is still enabled, it will then restart.

#### Input Overvoltage Fault Protection (OVLO)

The converter's input voltage is monitored to detect an input over voltage condition. When the input voltage is more than the  $V_{IN-OVLO+r}$ , a fault is detected, the powertrain stops switching, and the output voltage of the converter falls.

After an OVLO fault occurs, the converter will wait for the input voltage to fall below  $V_{IN-OVLO}$ . Provided the converter is still enabled, the powertrain will restart.

The powertrain controller itself also monitors the input voltage. Transient OVLO events which have not yet been detected by the fault sequence logic may first be detected by the controller if the input slew rate is sufficiently large. In this case, powertrain switching will immediately stop. If the input voltage falls back in range before the fault sequence logic detects the out of range condition, the powertrain will resume switching and the fault logic will not interrupt operation Regardless of whether the powertrain is running at the time or not, if the input voltage does not recover from OVLO before t<sub>OVLO</sub>, the converter fault logic will detect the fault.

#### **Output Undervoltage Fault Protection (UVP)**

The converter determines that an output overload or short circuit condition exists by measuring its primary sensed output voltage and the output of the internal error amplifier. In general, whenever the powertrain is switching and the primary-sensed output voltage falls below V<sub>OUT-UVP</sub> threshold, a short circuit fault will be registered. Once an output undervoltage condition is detected, the powertrain immediately stops switching, and the output voltage of the converter

falls. The converter remains disabled for a time  $t_{FAULT}$ . Once recovered and provided the converter is still enabled, the powertrain will again enter the soft start sequence after  $t_{INIT}$  and  $t_{ON}$ .

#### **Temperature Fault Protections (OTP)**

The fault logic monitors the internal temperature of the converter. If the measured temperature exceeds  $T_{INT-OTP}$ , a temperature fault is registered. As with the under voltage fault protection, once a temperature fault is registered, the powertrain immediately stops switching, the output voltage of the converter falls, and the converter remains disabled for at least time  $t_{FAULT}$ . Then, the converter waits for the internal temperature to return to below  $T_{INT-OTP}$  before recovering. Provided the converter is still enabled, the DCM will restart after  $t_{INIT}$  and  $t_{ON}$ .

#### **Output Overvoltage Fault Protection (OVP)**

The converter monitors the output voltage during each switching cycle by a corresponding voltage reflected to the primary side control circuitry. If the primary sensed output voltage exceeds V<sub>OUT-OVP</sub>, the OVP fault protection is triggered. The control logic disables the powertrain, and the output voltage of the converter falls.

This type of fault is latched, and the converter will not start again until the latch is cleared. Clearing the fault latch is achieved by either disabling the converter via the EN pin, or else by removing the input power such that the input voltage falls below V<sub>IN-INIT</sub>.

#### **External Output Capacitance**

The DCM converter internal compensation requires a minimum external output capacitor. An external capacitor in the range of 220 to 2200  $\mu$ F with ESR of 10 m $\Omega$  is required, per DCM for control loop compensation purposes.

However some DCM models require an increase to the minimum external output capacitor value in certain loading and trim condition. In applications where the load can go below 20% of rated load but the output trim is held constant, the range of output capacitor required is given by C<sub>OUT-EXT-TRANS</sub> in the Electrical Specifications table. If the load can go below 20% of rated load and the DCM output trim is also dynamically varied, the range of output capacitor required is given by C<sub>OUT-EXT-TRANS-TRIM</sub> in the Electrical Specifications table.

#### Light Load Boosting

Under light load conditions, the DCM converter may operate in light load boosting depending on the line voltage. Light load boosting occurs whenever the internal power consumption of the converter combined with the external output load is less than the minimum power transfer per switching cycle. In order to maintain regulation, the error amplifier will switch the powertrain off and on repeatedly, to effectively lower the average switching frequency, and permit operation with no external load. During the time when the power train is off, the module internal consumption is significantly reduced, and so there is a notable reduction in no-load input power in light load boosting. When the load is less than 20% of rated Iout, the output voltage may rise by a maximum of 2.4 V, above the output voltage calculated from trim, temperature, and load line conditions.



# DCM4623xD2K26E0y7z

#### Thermal Design

Based on the safe thermal operating area shown in page 5, the full rated power of the DCM4623xD2K26E0y7z can be processed provided that the top, bottom, and leads are all held below 80°C. These curves highlight the benefits of dual sided thermal management, but also demonstrate the flexibility of the Vicor ChiP platform for customers who are limited to cooling only the top or the bottom surface.

The OTP sensor is located on the top side of the internal PCB structure. Therefore in order to ensure effective over-temperature fault protection, the case bottom temperature must be constrained by the thermal solution such that it does not exceed the temperature of the case top.

The ChiP package provides a high degree of flexibility in that it presents three pathways to remove heat from internal power dissipating components. Heat may be removed from the top surface, the bottom surface and the leads. The extent to which these three surfaces are cooled is a key component for determining the maximum power that is available from a ChiP, as can be seen from Figure 17.

Since the ChiP has a maximum internal temperature rating, it is necessary to estimate this internal temperature based on a real thermal solution. Given that there are three pathways to remove heat from the ChiP, it is helpful to simplify the thermal solution into a roughly equivalent circuit where power dissipation is modeled as a current source, isothermal surface temperatures are represented as voltage sources and the thermal resistances are represented as resistors. Figure 17 shows the "thermal circuit" for a 4623 ChiP DCM, in an application where both case top and case bottom, and leads are cooled. In this case, the DCM power dissipation is PD<sub>TOTAL</sub> and the three surface temperatures are represented as T<sub>CASE\_TOP</sub>, T<sub>CASE\_BOTTOM</sub>, and T<sub>LEADS</sub>. This thermal system can now be very easily analyzed with simple resistors, voltage sources, and a current source.

This analysis provides an estimate of heat flow through the various pathways as well as internal temperature.




Figure 17 — Double side cooling and leads thermal model

Alternatively, equations can be written around this circuit and analyzed algebraically:

 $T_{INT} - PD_{1} \bullet \theta_{INT-TOP} = T_{CASE\_TOP}$   $T_{INT} - PD_{2} \bullet \theta_{INT-BOTTOM} = T_{CASE\_BOTTOM}$   $T_{INT} - PD_{3} \bullet \theta_{INT-LEADS} = T_{LEADS}$  $PD_{TOTAL} = PD_{1} + PD_{2} + PD_{3}$ 

Where  $T_{INT}$  represents the internal temperature and PD<sub>1</sub>, PD<sub>2</sub>, and PD<sub>3</sub> represent the heat flow through the top side, bottom side, and leads respectively.




Figure 18 — One side cooling and leads thermal model

Figure 18 shows a scenario where there is no bottom side cooling. In this case, the heat flow path to the bottom is left open and the equations now simplify to:

 $T_{INT} - PD_{1} \bullet \boldsymbol{\theta}_{INT-TOP} = T_{CASE\_TOP}$  $T_{INT} - PD_{3} \bullet \boldsymbol{\theta}_{INT-LEADS} = T_{LEADS}$  $PD_{TOTAL} = PD_{1} + PD_{3}$ 





Figure 19 — One side cooling thermal model

Figure 19 shows a scenario where there is no bottom side and leads cooling. In this case, the heat flow path to the bottom is left open and the equations now simplify to:

 $T_{INT} - PD_1 \bullet \boldsymbol{\theta}_{INT-TOP} = T_{CASE\_TOP}$  $PD_{TOTAL} = PD_1$ 





Vicor provides a suite of online tools, including a simulator and thermal estimator which greatly simplify the task of determining whether or not a DCM thermal configuration is sufficient for a given condition. These tools can be found at: <a href="http://www.vicorpower.com/powerbench">www.vicorpower.com/powerbench</a>.

DCMs in current limit will operate with higher output current or power than the rated levels. Therefore the Figure 20 Thermal Safe Operating Area plot should be used for loads that drive the DCM in to current limit for sustained operation.

#### **Standalone Operation**

The following Figure 21 shows the configuration of the Enhanced  $V_{OUT}$  DCM. An input filter is required to attenuate noise coming from the input source. In case of the excessive line inductance, a properly sized decoupling capacitor  $C_{DECOUPLE}$  is required as shown in the following figure.

If signal pins (TR, EN, FT) are not used, they can be left floating, and DCM will work in the nominal output condition.

When common mode noise in the input side is not a concern, TR and EN can be driven and FT received using -IN as a reference.

L1: 1 µH, minimized DCR;

**R1:** 1.0 Ω; **C1:** Ceramic capacitors in parallel, C1 = 2  $\mu$ F;

**L2:**  $L2 \ge 0.15$  uH:

**R2:** 1 Ω;


**C**<sub>OUTEXT</sub>: electrolytic or tantalum capacitor, 220  $\mu$ F  $\leq$  C3  $\leq$ 2200  $\mu$ F; **C4, C5**: additional ceramic /electrolytic capacitors, if needed for output ripple filtering;

In order to help sensitive signal circuits reject potential noise, additional components are recommended:

**R5:** 301  $\Omega$ , facilitate noise attenuation for TR pin;


**FB1, C2:** FB1 is a ferrite bead with an impedance of at least  $10 \Omega$  at 100MHz. **C2** can be a ceramic capacitor of  $0.1\mu$ F. Facilitate noise attenuation for EN pin.

Note: Use an RCR filter network as suggested in the application note AN:030 to reduce the noise on the signal pins.





 $\mathbf{VI}($ 



### **DCM Module Product Outline Drawing Recommended PCB Footprint and Pinout**

# **Revision History**

Revision	Date	Description	Page Number(s)
1.0	12/15/17	Initial release	n/a
1.1	01/29/20	Updated typical applications Output voltage regulation specification format change Updated state and timing diagrams Updated Trim descriptions and typical external circuits diagram	2 5 8 – 10 16, 17
1.2	08/31/20	Added MIL-STD info	1
1.3	11/06/20	Typo correction	1



#### Vicor's comprehensive line of power solutions includes high density AC-DC and DC-DC modules and accessory components, fully configurable AC-DC and DC-DC power supplies, and complete custom power systems.

Information furnished by Vicor is believed to be accurate and reliable. However, no responsibility is assumed by Vicor for its use. Vicor makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication. Vicor reserves the right to make changes to any products, specifications, and product descriptions at any time without notice. Information published by Vicor has been checked and is believed to be accurate at the time it was printed; however, Vicor assumes no responsibility for inaccuracies. Testing and other quality controls are used to the extent Vicor deems necessary to support Vicor's product warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

#### Specifications are subject to change without notice.

Visit http://www.vicorpower.com/dc-dc/isolated-regulated/dcm for the latest product information.

#### Vicor's Standard Terms and Conditions and Product Warranty

All sales are subject to Vicor's Standard Terms and Conditions of Sale, and Product Warranty which are available on Vicor's webpage (http://www.vicorpower.com/termsconditionswarranty) or upon request.

#### **Life Support Policy**

VICOR'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS PRIOR WRITTEN APPROVAL OF THE CHIEF EXECUTIVE OFFICER AND GENERAL COUNSEL OF VICOR CORPORATION. As used herein, life support devices or systems are devices which (a) are intended for surgical implant into the body, or (b) support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in a significant injury to the user. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system or to affect its safety or effectiveness. Per Vicor Terms and Conditions of Sale, the user of Vicor products and components in life support applications assumes all risks of such use and indemnifies Vicor against all liability and damages.

#### **Intellectual Property Notice**

Vicor and its subsidiaries own Intellectual Property (including issued U.S. and Foreign Patents and pending patent applications) relating to the products described in this data sheet. No license, whether express, implied, or arising by estoppel or otherwise, to any intellectual property rights is granted by this document. Interested parties should contact Vicor's Intellectual Property Department.

The products described on this data sheet are protected by the following U.S. Patents Numbers: RE40,072; 7,561,446; 7,920,391; 7,782,639; 8,427,269; 6,421,262 and other patents pending.

Contact Us: http://www.vicorpower.com/contact-us

#### **Vicor Corporation**

25 Frontage Road Andover, MA, USA 01810 Tel: 800-735-6200 Fax: 978-475-6715 www.vicorpower.com

#### email

Customer Service: custserv@vicorpower.com Technical Support: apps@vicorpower.com

©2017 – 2020 Vicor Corporation. All rights reserved. The Vicor name is a registered trademark of Vicor Corporation. All other trademarks, product names, logos and brands are property of their respective owners.

Rev 1.3

