

BCM[®] in a VIA[™] Package Bus Converter

BCM4414xH0E5035yzz



Isolated Fixed-Ratio DC-DC Converter

Features & Benefits

- Up to 35A continuous low-voltage-side current
- Fixed transformation ratio (K) of 1/16
- Up to 776W/in³ power density
- 97.7% peak efficiency
- Integrated filtering
- · Parallel operation for multi-kW arrays
- OV, OC, UV, short circuit and thermal protection
- 4414 package
- High MTBF
- · Thermally enhanced VIA package
- PMBus® management interface

Typical Applications

- High-Voltage DC Power Distribution
- 3-Phase AC-DC Converters
- Information and Communication Technology (ICT) Equipment
- High-End Computing Systems
- Automated Test Equipment
- Industrial Systems
- High-Density Energy Systems
- Transportation
- Green Buildings and Microgrids

Product Ratings						
V _{HI} = 650V (500 – 800V)	I_{LO} = up to 35A					
V _{LO} = 40.6V (31.3 – 50.0V) (NO LOAD)	K = 1/16					

Product Description

The BCM4414xH0E5035yzz in a VIA package is a high-efficiency Bus Converter, operating from a 500 to $800V_{DC}$ high-voltage bus to deliver an isolated 31.3 to $50.0V_{DC}$ unregulated, low voltage.

This unique ultra-low-profile module incorporates DC-DC conversion, integrated filtering and PMBus commands and controls in a chassis or PCB mount form factor.

The BCM offers low noise, fast transient response and industry-leading efficiency and power density. A low-voltage-side referenced PMBus-compatible telemetry and control interface provides access to the BCM's configuration, fault monitoring and other telemetry functions.

Leveraging the thermal and density benefits of Vicor VIA packaging technology, the BCM module offers flexible thermal management options with very low top- and bottom-side thermal impedances.


When combined with downstream Vicor DC-DC conversion components and regulators, the BCM allows the Power Design Engineer to employ a simple, low-profile design, which will differentiate the end system without compromising on cost or performance metrics.




Size: 4.35 x 1.40 x 0.37in [110.55 x 35.54 x 9.40mm]



Typical Applications




3-phase AC to point-of-load (3-phase AIM™ + BCM4414xH0E5035yzz)




Paralleling BCM in a VIA package – connection to common Host PMBus

Typical Applications (Cont.)




BCM4414xH0E5035yzz + PRM™ + VTM™, Adaptive-Loop Configuration – connection to common Host PMBus



BCM4414xH0E5035yzz + PRM + VTM, Remote-Sense Configuration – connection to common Host PMBus

Pin Configuration



Note: The dot on the VIA housing indicates the location of the signal pin 9.

Pin Descriptions

Pin Number	Signal Name	Туре	Function
1	+HI	HIGH SIDE POWER	High-voltage-side positive power terminal
2	-HI	HIGH SIDE POWER RETURN	High-voltage-side negative power terminal
3	+LO	LOW SIDE POWER	Low-voltage-side positive power terminal
4	-LO	LOW SIDE POWER RETURN	Low-voltage-side negative power terminal
5	EXT BIAS	INPUT	5V supply input
6	SCL	INPUT	I ² C™ Clock, PMBus® Compatible
7	SDA	INPUT/OUTPUT	I ² C Data, PMBus Compatible
8	SGND	LOW SIDE SIGNAL RETURN	Signal Ground
9	ADDR	INPUT	Address assignment – Resistor based

Notes: All signal pins (5, 6, 7, 8, 9) are referenced to the low-voltage side and isolated from the high-voltage side. Keep SGND signal separated from the low-voltage side power return terminal (–LO) in electrical design.



Part Ordering Information

Part Number	Package Type	Product Grade	Option Field	
BCM4414 B H0E5035 T06			06 = Short Pin/PMBus®	
BCM4414 B H0E5035 TR6		T = -40 to 100°C ^[a]	R6 = Reversible Short Pin/PMBus	
BCM4414 B H0E5035 T10		I = -40 to 100 C ¹⁵	10 = Long Pin/PMBus	
BCM4414 B H0E5035 TR0	B = Board VIA		R0 = Reversible Long Pin/PMBus	
BCM4414 B H0E5035 M06			06 = Short Pin/PMBus	
BCM4414 B H0E5035 MR6		M = -55 to 100°C ^[a]	R6 = Reversible Short Pin/PMBus	
BCM4414 B H0E5035 M10		IVI = −55 to 100°C to	10 = Long Pin/PMBus	
BCM4414 B H0E5035 MR0			R0 = Reversible Long Pin/PMBus	
BCM4414 V H0E5035 T02		T = -40 to 100°C ^[a]	02 = Chassis/PMBus	
BCM4414 V H0E5035 TR2	V = Chassis VIA	I = -40 to 100 C to	R2 = Reversible Chassis/PMBus	
BCM4414 V H0E5035 M02	V = CIIdSSIS VIA	M = -55 to 100°C ^[a]	02 = Chassis/PMBus	
BCM4414 V H0E5035 MR2		$ V = -22 \text{ for } 100^{\circ}\text{C}^{-101}$	R2 = Reversible Chassis/PMBus	

[[]a] High-temperature current de-rating may apply; see Figure 1, specified thermal operating area.

Absolute Maximum Ratings

The absolute maximum ratings below are stress ratings only. Operation at or beyond these maximum ratings can cause permanent damage to the device.

Parameter	Comments	Min	Max	Unit
+HI to –HI		-1	900	V
HI_DC or LO_DC Slew Rate			1	V/µs
+LO to -LO		-1	60	V
EVT DIAC to CCND		-0.3	10	V
EXT BIAS to SGND			0.15	А
SCL to SGND		-0.3	5.5	V
SDA to SGND		-0.3	5.5	V
ADDR to SGND		-0.3	3.6	V
	High-voltage side to case	3100		V _{DC}
Isolation Voltage / Dielectric Withstand	High-voltage side to low-voltage side	4300		V _{DC}
	Low-voltage side to case	1200		V _{DC}

Electrical Specifications

Specifications apply over all line and load conditions, unless otherwise noted; **boldface** specifications apply over the temperature range of $-40^{\circ}\text{C} \leq T_{\text{CASE}} \leq 100^{\circ}\text{C}$ (T-Grade); all other specifications are at $T_{\text{CASE}} = 25^{\circ}\text{C}$ unless otherwise noted.

Attribute	Symbol Conditions / Notes		Min	Тур	Max	Unit
	rtrain Specificati	on – Forward Direction Operation (High-Voltage Si	de to Low	-Voltage Si	ide)	
HI-Side Voltage Range, (Continuous)	V_{HI_DC}		500		800	V
HI-Side Voltage Range, (Transient)	V _{HI_TRANS}		500		800	V
HI-Side Voltage Initialization Threshold	V _{µC_ACTIVE}	HI-side voltage where internal controller is initialized, (powertrain inactive)	130		350	V
III Sida Quiassant Current	1	Disabled, V _{HL_DC} = 650V		6.3		700 A
HI-Side Quiescent Current	I_{HI_Q}	T _{CASE} ≤ 100°C			10.2	mA
		V _{HI_DC} = 650V, T _{CASE} = 25°C		14	23	
Ne Leed Device Dissipation	D	V _{HL_DC} = 650V			37	10/
No-Load Power Dissipation	P_{HI_NL}	V _{HI_DC} = 500 – 800V, T _{CASE} = 25°C			25	W
		V _{HI_DC} = 500 – 800V			39	
HI-Side Inrush Current Peak	lhi inr pk	$V_{HL,DC} = 800V$, $C_{LO,EXT} = 470 \mu F$, $R_{LOAD,LO} = 20\%$ of full-load current		5		А
	111_11411_114	T _{CASE} ≤ 100°C			10	
DC HI-Side Current	I _{HI_IN_DC}	At $I_{LO_OUT_DC} = 35A$, $T_{CASE} \le 70^{\circ}C$			2.3	А
Transformation Ratio	К	High voltage to low voltage $K = V_{LO_DC} / V_{HI_DC}$, at no load		1/16		V/V
LO-Side Current (Continuous)	I _{LO_OUT_DC}	T _{CASE} ≤ 70°C			35	А
LO-Side Current (Pulsed)	I _{LO_OUT_PULSE}	2ms pulse, 25% duty cycle, $I_{LO_OUT_AVG} \le 50\% \text{ rated } I_{LO_OUT_DC}$			40	А
		V _{HI_DC} = 650V, I _{LO_OUT_DC} = 35A	96.0	97.2		
Efficiency (Ambient)	η_{AMB}	V _{HI_DC} = 500 – 800V, I _{LO_OUT_DC} = 35A	94.7			%
		$V_{HI_DC} = 650V$, $I_{LO_OUT_DC} = 17.5A$	95.3	97.5		
Efficiency (Hot)	η_{HOT}	V _{HI_DC} = 650V, I _{LO_OUT_DC} = 35A, T _{CASE} = 70°C	96.8	97.4		%
Efficiency (Over Load Range)	η _{20%}	7A < I _{LO_OUT_DC} < 35A	91			%
	R _{LO_COLD}	$V_{HI_DC} = 650V$, $I_{LO_OUT_DC} = 35A$, $T_{CASE} = -40$ °C	3	9.6	18	
LO-Side Output Resistance	R _{LO_AMB}	V _{HI_DC} = 650V, I _{LO_OUT_DC} = 35A	7	13.8	20	mΩ
	R _{LO_HOT}	V _{HI_DC} = 650V, I _{LO_OUT_DC} = 35A, T _{CASE} = 70°C	7	16.2	25	
Switching Frequency	F _{SW}	LO-side voltage ripple frequency = 2x F _{SW}	0.8	0.9	1.0	MHz
LO-Side Voltage Ripple	V _{LO_OUT_PP}	$C_{LO_EXT} = 0\mu F$, $I_{LO_OUT_DC} = 35A$, $V_{HI_DC} = 650V$, $20MHz~BW$		500		mV
J 11	23_001_11	T _{CASE} ≤ 100°C			800	



Electrical Specifications (Cont.)

Specifications apply over all line and load conditions, unless otherwise noted; **boldface** specifications apply over the temperature range of $-40^{\circ}\text{C} \leq T_{\text{CASE}} \leq 100^{\circ}\text{C}$ (T-Grade); all other specifications are at $T_{\text{CASE}} = 25^{\circ}\text{C}$ unless otherwise noted.

Attribute	Symbol	Conditions / Notes		Тур	Max	Unit				
General Powertrain Specification – Forward Direction Operation (High-Voltage Side to Low-Voltage Side) Cont.										
Effective HI-Side Capacitance (Internal)	C _{HI_INT}	Effective value at 650V _{HLDC}		0.16		μF				
Effective LO-Side Capacitance (Internal)	C _{LO_INT}	Effective value at 40.6V _{LO_DC}		43.2		μF				
Rated LO-Side Capacitance (External)	C _{LO_OUT_EXT}	Excessive capacitance may drive module into short circuit protection			470	μF				
Rated LO-Side Capacitance (External), Parallel Array Operation	C _{LO_OUT_AEXT}	$C_{LO_OUT_AEXT}$ Max = N • 0.5 • $C_{LO_OUT_EXT\ MAX}$, where N = the number of units in parallel			235	μF				

Powertrain Hardware Protection Specification – Forward Direction Operation (High-Voltage Side to Low-Voltage Side)

- These built-in powertrain protections are fixed in hardware and cannot be configured through PMBus®.
- When duplicated in supervisory limits, hardware protections serve a secondary role and become active when supervisory limits are disabled through PMBus.

Auto Restart Time	t _{AUTO_RESTART}	Start up into a persistent fault condition. Non-latching fault detection given $V_{Hl_DC} > V_{Hl_UVLO+}$	900	1000	1100	ms
HI-Side Overvoltage Lockout Threshold	V _{HI_OVLO+}		830	860	880	V
HI-Side Overvoltage Recovery Threshold	V _{HI_OVLO} _		800	830	850	V
HI-Side Overvoltage Lockout Hysteresis	V _{HI_OVLO_HYST}			20		V
HI-Side Overvoltage Lockout Response Time	t _{HI_OVLO}			10		μs
HI-Side Soft Start Time	t _{HI_SOFT_START}	From powertrain active. Fast current limit protection disabled during soft start		1	2	ms
LO-Side Overcurrent Trip Threshold	I _{LO_OUT_OCP}		37	50	70	А
LO-Side Overcurrent Response Time Constant	t _{LO_OUT_OCP}	Effective internal RC filter		3.6		ms
LO-Side Short Circuit Protection Trip Threshold	I _{LO_OUT_SCP}	Short-circuit protection (fast current limit) is disabled at start up [b]	55			А
LO-Side Short Circuit Protection Response Time	t _{LO_OUT_SCP}			1		μs
Overtemperature Shut-Down Threshold	t _{OTP+}	Internal	125			°C

[[]b] At start up, short circuit protection is disabled. Soft-start current limit provides protection against pre-existing output shorts. Soft-start mode ends when the output voltage reaches at least 90% of the final output voltage, and short-circuit protection is enabled when t_{HL_SOFT_START} expires. Shorts that occur after soft start ends but before t_{HL_SOFT_START} expires may cause damage to the product and will require external protection.



Electrical Specifications (Cont.)

Specifications apply over all line and load conditions, unless otherwise noted; **boldface** specifications apply over the temperature range of $-40^{\circ}\text{C} \leq T_{\text{CASE}} \leq 100^{\circ}\text{C}$ (T-Grade); all other specifications are at $T_{\text{CASE}} = 25^{\circ}\text{C}$ unless otherwise noted.

Attribute	Symbol	Conditions / Notes	Min	Тур	Max	Unit
Powertrain Superviso	ry Limits Speci	fication – Forward Direction Operation (High-Volta	ge Side to	Low-Volta	age Side)	
		roller and can be reconfigured or disabled through PMBus ted in the previous table will intervene during fault events				
HI-Side Overvoltage Lockout Threshold	V _{HI_OVLO+}		830	860	880	V
HI-Side Overvoltage Recovery Threshold	V _{HI_OVLO} _		800	830	850	V
HI-Side Overvoltage Lockout Hysteresis	V _{HI_OVLO_HYST}			20		V
HI-Side Overvoltage Lockout Response Time	t _{HI_OVLO}			100		μs
HI-Side Undervoltage Lockout Threshold	V _{HI_UVLO} _		430	450	470	V
HI-Side Undervoltage Recovery Threshold	V _{HI_UVLO+}		470	480	499	V
HI-Side Undervoltage Lockout Hysteresis	V _{HI_UVLO_HYST}			20		V
HI-Side Undervoltage Lockout Response Time	t _{HI_UVLO}			100		μs
HI-Side Undervoltage Start Up Delay	t _{HI_UVLO+_DELAY}	From $V_{HI_DC} = V_{HI_UVLO+}$ to powertrain active (i.e., one-time start up delay from application of V_{HI_DC} to V_{LO_DC})		50		ms
LO-Side Overcurrent Trip Threshold	I _{LO_OUT_OCP}		37	50	60	А
LO-Side Overcurrent Response Time Constant	t _{LO_OUT_OCP}	Effective internal RC filter		2		ms
Overtemperature Shut-Down Threshold	t _{OTP+}	Internal	125			°C
Overtemperature Recovery Threshold	t _{OTP}	Internal	105	110	115	°C
Undertemperature	+	T-Grade			-45	°C
Shut-Down Threshold (Internal)	t _{UTP}	M-Grade			-55	
Undertemperature Restart Time	t _{UTP_RESTART}	Start up into a persistent fault condition. Non-latching fault detection given $V_{Hl_DC} > V_{Hl_UVLO+}$		3		S



Electrical Specifications (Cont.)

Specifications apply over all line and load conditions, unless otherwise noted; **boldface** specifications apply over the temperature range of $-40^{\circ}\text{C} \leq T_{\text{CASE}} \leq 100^{\circ}\text{C}$ (T-Grade); all other specifications are at $T_{\text{CASE}} = 25^{\circ}\text{C}$ unless otherwise noted.

Attribute Symbol		Conditions / Notes	Min	Тур	Max	Unit	
General Powertra	ain Specificati	ion – Reverse-Direction Operation (Low-Voltage Si	de to High	-Voltage Si	de)		
LO-Side Input Voltage Range	V_{LO_DC}		31.25	40.63	50	V	
		$V_{LO_DC} = 40.63V, T_{CASE} = 25^{\circ}C$		12	18		
LO to HI No-Load Power Dissipation	P_{LO_NL}	$V_{LO_DC} = 40.63V$	6		25	W	
LO to Til No Lodd Tower Dissipation	' LO_NL	$V_{LO_DC} = 31.25 - 50V, T_{CASE} = 25^{\circ}C$			20	• • •	
		$V_{LO_DC} = 31.25 - 50V$			28		
DC LO-Side Input Current	I _{LO_IN_DC}	$I_{HI_DC} = 2.6A$, $T_{INTERNAL} \le 100$ °C			41	А	
HI-Side Output Power (Continuous)	P _{HI_OUT_DC}	Specified at $V_{LO_DC} = 40.63V$			1500	W	
HI-Side Output Power (Pulsed)	P _{HI_OUT_PULSE}	Specified at V_{LO_DC} = 40.63V, 2ms pulse, 25% duty cycle, $P_{HI_AVG} \le 50\%$ of rated $P_{HI_OUT_DC}$			2000	W	
HI-Side Output Current (Continuous)	I _{HI_OUT_DC}				2.2	А	
HI-Side Output Current (Pulsed)	I _{HI_OUT_PULSE}	2ms pulse, 25% duty cycle, $P_{HLAVG} \le 50\%$ of rated P_{HLOUT_DC}			2.5	А	
		$V_{LO_DC} = 40.63V$, $I_{HI_OUT_DC} = 2.21A$	96	97.1			
LO to HI Efficiency (Ambient)	η_{AMB}	V _{LO_DC} = 31.25- 50V, I _{HI_OUT_DC} = 2.21A	94.7			%	
		V _{LO_DC} = 40.63V, I _{HI_OUT_DC} = 1.11A	95.3	97.5			
LO to HI Efficiency (Hot)	η_{HOT}	$V_{LO_DC} = 40.63V$, $I_{HI_OUT_DC} = 2.21A$, $T_{CASE} = 70$ °C	96.3	97.2		%	
LO to HI Efficiency (Over Load Range)	η	0.21A < I _{HI_OUT_DC} < 2.21A	87			%	
	R _{HI_COLD}	$V_{LO_DC} = 40.63V$, $I_{HI_OUT_DC} = 2.21A$, $T_{CASE} = -40$ °C	5000	7100	9000		
LO to HI Output Resistance	R _{HI_AMB}	V _{LO_DC} = 40.63V, I _{HI_OUT_DC} = 2.21A, T _{CASE} = 25°C	6000	8200	10000	mΩ	
	R _{HI_HOT}	$V_{LO_DC} = 40.63V$, $I_{HI_OUT_DC} = 2.21A$, $T_{CASE} = 70$ °C	8000	10000	12000		
HI-Side Output Voltage Ripple	V _{HI OUT PP}	$C_{HI_OUT_EXT} = 0\mu F$, $I_{HI_OUT_DC} = 2.21A$, $V_{LO_DC} = 40.63V$, $20MHz~BW$		500		mV	
	* HI_OUT_PP	T _{CASE} = -40 to 70°C			1300		
Powertrain Hardware P	rotection Spe	cification – Reverse-Direction Operation (Low-Volt	age Side to	High-Volt	age Side)		
LO-Side Overvoltage Lockout Threshold	V _{LO_OVLO+}	Module latched shut down with $V_{HI_DC} < V_{HI_UVLO-_R}$	51.8	53.75	55	V	
LO-Side Overvoltage Response Time	t _{HI_OVLO}			100		us	
LO-Side Undervoltage Lockout Threshold	V _{LO_UVLO} _	Module latched shut down with $V_{HI_DC} < V_{HI_UVLO-_R}$	26.8	28	29.3	V	
LO-Side Undervoltage Response Time	t _{LO_UVLO}			100		μs	
HI-Side Undervoltage Lockout Threshold	V _{HI_UVLO} R	Based on threshold set in forward direction	430	450	470	V	
HI-Side Undervoltage Recovery Threshold	V _{HI_UVLO+_R}	No restart in reverse, unit latches off; reverse-mode bootstrap needed					
HI-Side Output Overcurrent Trip Threshold	I _{HI_OUT_OCP}	Module latched shut down with $V_{HI_DC} < V_{HI_UVLO-_R}$	2.3	3.1	4.3	А	
HI-Side Output Overcurrent Response Time	t _{HI_OUT_OCP}	Effective internal RC filter		3		ms	
HI-Side Output Short Circuit Protection Trip Threshold	I _{HI_OUT_SCP}	Module latched shut down with $V_{HI_DC} < V_{HI_UVLO-_R}$	3.4			А	
HI-Side Output Short Circuit Protection Response Time	t _{HI_OUT_SCP}			1		μs	



Operating Area




Figure 1 — Specified thermal operating area

- 1. The BCM in a VIA package is cooled through the non-pin-side case.
- 2. The thermal rating is based on typical measured device efficiency.
- 3. The case temperature in the graph is the measured temperature of the non-pin-side housing, such that the internal operating temperature does not exceed 125°C.




Figure 2 — Specified electrical operating area using rated $R_{LO\ HOT}$




Figure 3 — Specified HI-side start up into load current and external capacitance



PMBus® Reported Characteristics

Specifications apply over all line and load conditions, unless otherwise noted; **boldface** specifications apply over the temperature range of $-40^{\circ}\text{C} \leq T_{\text{CASE}} \leq 100^{\circ}\text{C}$ (T-Grade); all other specifications are at $T_{\text{CASE}} = 25^{\circ}\text{C}$ unless otherwise noted.

Monitored Telemetry

• The current telemetry is only available in forward operation. The input and output current reported value is not supported in reverse operation.

Attribute	PMBus Read Command	Accuracy (Rated Range)	Functional Reporting Range	Update Rate	Reported Units
HI-Side Voltage	(88h) READ_VIN	±5% (LL – HL)	130 to 880V	100µs	$V_{ACTUAL} = V_{REPORTED} \times 10^{-1}$
HI-Side Current	(89h) READ_IIN	±20% (10 – 20% of FL) ±5% (20 – 133% of FL)	-0.85 to 4.0A	100μs	$I_{ACTUAL} = I_{REPORTED} \times 10^{-3}$
LO-Side Voltage ^[c]	(8Bh) READ_VOUT	±5% (LL – HL)	8.125 to 55V	100µs	$V_{ACTUAL} = V_{REPORTED} \times 10^{-1}$
LO-Side Current	(8Ch) READ_IOUT	±20% (10 – 20% of FL) ±5% (20 – 133% of FL)	-13.6 to 60A	100µs	$I_{ACTUAL} = I_{REPORTED} \times 10^{-2}$
LO-Side Resistance	(D4h) READ_ROUT	±5% (50 – 100% of FL) at NL ±10% (50 – 100% of FL)(LL – HL)	5 to 40mΩ	100ms	$R_{ACTUAL} = R_{REPORTED} \times 10^{-5}$
Temperature ^[d]	(8Dh) READ_TEMPERATURE_1	±7°C (Full Range)	−55 to 130°C	100ms	$T_{ACTUAL} = T_{REPORTED}$

 $^{^{[}c]}$ Default READ LO Side Voltage returned when unit is disabled = -300V.

Variable Parameters

- Factory setting of all Thresholds and Warning limits listed below are 100% of specified protection values.
- \bullet Variables can be written only when module is disabled with $V_{HI} < V_{HI_UVLO-}$ and external bias (VDDB) applied.
- Module must remain in a disabled mode for 3ms after any changes to the variables below to allow sufficient time to commit changes to EEPROM.

Attribute	PMBus Command	Conditions / Notes	Accuracy (Rated Range)	Functional Reporting Range	Default Value
HI-Side Overvoltage Protection Limit	(55h) VIN_OV_FAULT_LIMIT	V _{HLOVLO} is automatically 3% lower than this set point	±5% (LL – HL)	130 – 850V	100%
HI-Side Overvoltage Warning Limit	(57h) VIN_OV_WARN_LIMIT		±5% (LL – HL)	130 – 820V	100%
HI-Side Undervoltage Protection Limit	(D7h) DISABLE_FAULTS	Can only be disabled to a preset default value	±5% (LL – HL)	130 – 500V	100%
HI-Side Overcurrent Protection Limit	(5Bh) IIN_OC_FAULT_LIMIT		±20% (10 – 20% of FL) ±5% (20 – 133% of FL)	0 – 4.0A	100%
HI-Side Overcurrent Warning Limit	(5Dh) IIN_OC_WARN_LIMIT		±20% (10 – 20% of FL) ±5% (20 – 133% of FL)	0 – 4.0A	100%
Overtemperature Protection Limit	(4Fh) OT_FAULT_LIMIT	Internal temperature	±7°C (Full Range)	0 – 125°C	100%
Overtemperature Warning Limit	(51h) OT_WARN_LIMIT	Internal temperature	±7°C (Full Range)	0 – 125°C	100%
Turn On Delay	(60h) TON_DELAY	Additional time delay to the undervoltage start up delay	±50µs	0 – 100ms	0ms



[[]d] Default READ Temperature returned when unit is disabled = -273°C.

Signal Characteristics

Specifications apply over all line and load conditions, unless otherwise noted; **boldface** specifications apply over the temperature range of $-40^{\circ}\text{C} \leq T_{\text{CASE}} \leq 100^{\circ}\text{C}$ (T-Grade); all other specifications are at $T_{\text{CASE}} = 25^{\circ}\text{C}$ unless otherwise noted. **Please note:** For chassis mount model, Vicor part number 42550 will be needed for applications requiring the use of the signal pins. Signal cable 42550 is rated up to five insertions and extractions. To avoid unnecessary stress on the connector, the cable should be appropriately strain relieved.

EXT. BIAS (VDDB) Pin

- VDDB powers the internal controller.
- VDDB needs to be applied to enable and disable the BCM through PMBus[®] control (using OPERATION COMMAND), and to adjust warning and protection thresholds.
- VDDB voltage not required for telemetry; however, if VDDB is not applied, telemetry information will be lost when V_{IN} is removed.

Signal Type	State	Attribute	Symbol	Conditions / Notes	Min	Тур	Max	Unit
Regular	VDDB Voltage	V_{VDDB}		4.5	5	9	V	
lanut	Operation	VDDB Current Consumption	I _{VDDB}				50	mA
Input	Start Up	Inrush Current Peak	I _{VDDB_INR}	V_{VDDB} slew rate = $1V/\mu s$		3.5		А
		Turn-On Time	t _{VDDB_ON}	From V _{VDDB_MIN} to PMBus active		1.5		ms

SGND Pin

- All PMBus interface signals (SCL, SDA, ADDR) are referenced to SGND pin.
- SGND pin also serves as return pin (ground pin) for VDDB.
- Keep SGND signal separated from the low-voltage side power return terminal (-LO) in electrical design.

Address (ADDR) Pin

- This pin programs the address using a resistor between ADDR pin and signal ground.
- The address is sampled during start up and is stored until power is reset. This pin programs only a Fixed and Persistent address.
- This pin has an internal $10k\Omega$ pullup resistor to 3.3V.
- 16 addresses are available. The range of each address is 206.25mV (total range for all 16 addresses is 0 3.3V).

Signal Type	State	Attribute	Symbol	Conditions / Notes	Min	Тур	Max	Unit
	Regular	ADDR Input Voltage	V_{SADDR}	See address section	0		3.3	V
Multi-Level Input	Operation	ADDR Leakage Current	I _{SADDR}	Leakage current			1	μΑ
,	Start Up	ADDR Registration Time	t _{SADDR}	From V _{VDDB_MIN}		1		ms




Signal Characteristics

Specifications apply over all line and load conditions, unless otherwise noted; **boldface** specifications apply over the temperature range of $-40^{\circ}\text{C} \leq T_{\text{CASE}} \leq 100^{\circ}\text{C}$ (T-Grade); all other specifications are at $T_{\text{CASE}} = 25^{\circ}\text{C}$ unless otherwise noted. **Please note:** For chassis mount model, Vicor part number 42550 will be needed for applications requiring the use of the signal pins. Signal cable 42550 is rated up to five insertions and extractions. To avoid unnecessary stress on the connector, the cable should be appropriately strain relieved.

Serial Clock input (SCL) AND Serial Data (SDA) Pins


- High-power SMBus specification and SMBus physical layer compatible. Note that optional SMBALERT# is not supported.
- PMBus® command compatible.

Signal Type	State	Attribute	Symbol	Conditions / Notes	Min	Тур	Max	Unit
		Electrical Parameters						
		Innut Valtage Threehold	V _{IH}		2.1			V
		Input Voltage Threshold	V _{IL}				0.8	V
		Output Voltage Threshold	V _{OH}		3			V
		Output voitage Threshold	V _{OL}				0.4	V
		Leakage Current	I _{LEAK_PIN}	Unpowered device			10	μΑ
		Signal Sink Current	I _{LOAD}	V _{OL} = 0.4V	4			mA
		Signal Capacitive Load	C _I	Total capacitive load of one device pin			10	рF
		Signal Noise Immunity	V _{NOISE_PP}	10 – 100MHz	300			mV
		Timing Parameters						
	Regular Operation	Operating Frequency	F _{SMB}	Idle state = 0Hz	10		400	kHz
Digital		Free Time Between Stop and Start Condition	t _{BUF}		1.3			μs
Input/Output		Hold Time After Start or Repeated Start Condition	t _{HD:STA}	First clock is generated after this hold time	0.6			μs
		Repeat Start Condition Set-Up Time	t _{SU:STA}		0.6			μs
		Stop Condition Set-Up Time	t _{SU:STO}		0.6			μs
		Data Hold Time	t _{HD:DAT}		300			ns
		Data Set-Up Time	t _{SU:DAT}		100			ns
		Clock Low Timeout	t _{TIMEOUT}		25		35	ms
		Clock Low Period	t _{LOW}		1.3			μs
		Clock High Period	t _{HIGH}		0.6		50	μs
		Cumulative Clock Low Extend Time	t _{LOW:SEXT}				25	ms
		Clock or Data Fall Time	t _F		20		300	ns
		Clock or Data Rise Time	t _R		20		300	ns





Timing Diagram (Forward Direction)





Application Characteristics

Temperature controlled via pin-side cold plate, unless otherwise noted. All data presented in this section are collected from units processing power in the forward direction (high-voltage side to low-voltage side). See associated figures for general trend data.




Figure 4 — No-load power dissipation vs. V_{HI_DC}




Figure 6 — Efficiency at $T_{CASE} = -55$ °C




Figure 8 — Efficiency at $T_{CASE} = 25^{\circ}C$




Figure 5 — Full-load efficiency vs. temperature




Figure 7 — Power dissipation at $T_{CASE} = -55$ °C




Figure 9 — Power dissipation at $T_{CASE} = 25^{\circ}C$

Application Characteristics (Cont.)

Temperature controlled via pin-side cold plate, unless otherwise noted. All data presented in this section are collected from units processing power in the forward direction (high-voltage side to low-voltage side). See associated figures for general trend data.




Figure 10 — Efficiency at $T_{CASE} = 70$ °C




Figure 12 — R_{LO} vs. temperature; nominal V_{HI_DC} , I_{LO_DC} = 35A




Figure 11 — Power dissipation at $T_{CASE} = 70^{\circ}C$




Figure 13 — $V_{LO_OUT_PP}$ vs. I_{LO_DC} ; no external $C_{LO_OUT_EXT.}$ Board-mounted module, scope setting: 20MHz analog BW

Application Characteristics (Cont.)

Temperature controlled via pin-side cold plate, unless otherwise noted. All data presented in this section are collected from units processing power in the forward direction (high-voltage side to low-voltage side). See associated figures for general trend data.




Figure 14 — Full-load LO-side voltage ripple, no external C_{HI_IN_EXT}; no external C_{LO_OUT_EXT}. Board-mounted module, scope setting: 20MHz analog BW




Figure 16 — 35 – 0A transient response: no external $C_{HI_IN_EXT}$ no external $C_{LO_OUT_EXT}$




Figure 18 — Start up from application of OPERATION COMMAND with pre-applied V_{HI_DC} = 650V, 20% I_{LO_DC} 100% $C_{LO_OUT_EXT}$




Figure 15 — 0 – 35A transient response: no external $C_{HI_IN_EXT}$ no external $C_{LO_OUT_EXT}$




Figure 17 — Start up from application of V_{HI_DC} = 650V, 20% I_{LO_DC} 100% $C_{LO_OUT_EXT}$

General Characteristics

Specifications apply over all line and load conditions, unless otherwise noted; **boldface** specifications apply over the temperature range of $-40^{\circ}\text{C} \leq T_{\text{CASE}} \leq 100^{\circ}\text{C}$ (T-Grade); all other specifications are at $T_{\text{CASE}} = 25^{\circ}\text{C}$ unless otherwise noted.

Attribute	Symbol	Conditions / Notes	Min	Тур	Max	Unit	
		March Start					
l an artic		Mechanical	110 20 [4 24]	110 55 [4 25]	110 00 [4 26]	[:-1	
Length	L	Lug (Chassis) Mount	110.30 [4.34]	110.55 [4.35]	110.80 [4.36]	mm [in]	
Length	L	PCB (Board) Mount	112.51 [4.43]	112.76 [4.44]	113.01 [4.45]	mm [in]	
Width	W		35.29 [1.39]	35.54 [1.40]	35.79 [1.41]	mm [in]	
Height	H		9.019 [0.355]	9.40 [0.37]	9.781 [0.385]	mm [in]	
Volume	Vol	Without heatsink		36.93 [2.25]		cm³ [in³]	
Weight	W			145 [5.115]		g [oz]	
Pin Material		C145 copper					
Underplate		Low-stress ductile Nickel	50		100	μin	
Pin Finish (Gold)		Palladium	0.8		6	μin	
Till Tillisi (Gold)		Soft Gold	0.12		2	РП	
Pin Finish (Tin)		Whisker-resistant matte Tin	200		400	μin	
		Thermal					
0 1 1 17	-	BCM4414xH0E5035yzz (T-Grade)	-40		125	°C	
Operating Internal Temperature	T _{INT}	BCM4414xH0E5035yzz (M-Grade)	-55		125	٥	
		BCM4414xH0E5035yzz (T-Grade), de-rating applied, see safe thermal operating area	-40		100		
Operating Case Temperature	T _{CASE}	BCM4414xH0E5035yzz (M-Grade), de-rating applied, see safe thermal operating area	-55		100	°C	
Thermal Resistance Pin Side	$\theta_{\text{INT_PIN_SIDE}}$	Estimated thermal resistance to maximum temperature internal component from isothermal pin/terminal-side housing		1.5		°C/W	
Thermal Resistance Housing	θ_{HOU}	Estimated thermal resistance of thermal coupling between the pin-side and non-pin-side case surfaces		0.29		°C/W	
Thermal Resistance Non-Pin Side	$\theta_{\text{INT_NON_PIN_SIDE}}$	Estimated thermal resistance to maximum temperature internal component from isothermal non-pin/non-terminal housing		1.5		°C/W	
Thermal Capacity		<u> </u>		54		Ws/°C	
	'	Assembly	'				
	_	BCM4414xH0E5035yzz (T-Grade)	-40		125		
Storage Temperature	T _{ST}	BCM4414xH0E5035yzz (M-Grade)	-65		125	°C	
	ESD _{HBM}	Human Body Model, "ESDA / JEDEC JDS-001-2012" Class I-C (1kV to < 2kV)	1000				
ESD Withstand	ESD _{CDM}	Charge Device Model, "JESD 22-C101-E" Class II (200V to < 500V)	200				



General Characteristics (Cont.)

Specifications apply over all line and load conditions, unless otherwise noted; **boldface** specifications apply over the temperature range of $-40^{\circ}\text{C} \leq T_{\text{CASE}} \leq 100^{\circ}\text{C}$ (T-Grade). All other specifications are at $T_{\text{CASE}} = 25^{\circ}\text{C}$ unless otherwise noted.

Attribute	Symbol	Conditions / Notes	Min	Тур	Max	Unit	
		Safety					
Isolation Capacitance	C _{HI_LO}	Unpowered unit	620	780	940	pF	
Isolation Resistance	R _{HI_LO}	At 500V _{DC}	10			ΜΩ	
MTBF		MIL-HDBK-217Plus Parts Count - 25°C Ground Benign, Stationary, Indoors / Computer		2.51		MHrs	
		Telcordia Issue 2 - Method I Case III; 25°C Ground Benign, Controlled		5.82		MHrs	
		cTÜVus EN 60950-1					
Agency Approvals / Standards		cURus UL 60950-1					
		CE Marked for Low Voltage Directive and	able				



BCM in a VIA Package




Figure 19 — BCM DC model (Forward Direction)

The BCM uses a high-frequency resonant tank to move energy from the high-voltage side to the low-voltage side and vice versa. The resonant LC tank, operated at high frequency, is amplitude modulated as a function of the HI-side voltage and the LO-side current. A small amount of capacitance embedded in the high-voltage-side and low-voltage-side stages of the module is sufficient for full functionality and is key to achieving high power density.

The BCM4414xH0E5035yzz can be simplified into the model shown in Figure 19.

At no load:

$$V_{LO} = V_{HI} \bullet K \tag{1}$$

K represents the "turns ratio" of the BCM. Rearranging Equation 1:

$$K = \frac{V_{LO}}{V_{UI}} \tag{2}$$

In the presence of a load, V_{LO} is represented by:

$$V_{LO} = V_{HI} \bullet K - I_{LO} \bullet R_{LO} \tag{3}$$

and I_{LO} is represented by:

$$I_{LO} = \frac{I_{HI} - I_{HI_Q}}{K} \tag{4}$$

 R_{LO} represents the impedance of the BCM and is a function of the R_{DS_ON} of the HI-side and LO-side MOSFETs, PC board resistance of HI-side and LO-side boards and the winding resistance of the power transformer. I_{HI_Q} represents the HI-side quiescent current of the BCM controller, gate drive circuitry and core losses.

The effective DC voltage transformer action provides additional interesting attributes. Assuming that $R_{LO} = 0\Omega$ and $I_{HI_Q} = 0A$, Equation 3 now becomes Equation 1 and is essentially load independent, resistor R is now placed in series with V_{HI} .




Figure 20 — K = 1/16 BCM with series HI-side resistor

The relationship between V_{HI} and V_{LO} becomes:

$$V_{LO} = (V_{HI} - I_{HI} \bullet R) \bullet K \tag{5}$$

Substituting the simplified version of Equation 4 (I_{HLO} is assumed = 0A) into Equation 5 yields:

$$V_{LO} = V_{HI} \bullet K - I_{LO} \bullet R \bullet K^2 \tag{6}$$

This is similar in form to Equation 3, where R_{LO} is used to represent the characteristic impedance of the BCM. However, in this case a real resistor, R, on the high-voltage side of the BCM is effectively scaled by K^2 with respect to the low-voltage side.

Assuming that $R = 1\Omega$, the effective R as seen from the low-voltage side is $3.9m\Omega$, with K = 1/16.

A similar exercise can be performed with the addition of a capacitor or shunt impedance at the high-voltage side of the BCM. A switch in series with $V_{\rm HI}$ is added to the circuit. This is depicted in Figure 21.




Figure 21 — BCM with HI-side capacitor

A change in $V_{\rm HI}$ with the switch closed would result in a change in capacitor current according to the following equation:

$$I_C(t) = C \frac{dV_{HI}}{dt} \tag{7}$$

Assume that with the capacitor charged to V_{HI} , the switch is opened and the capacitor is discharged through the idealized BCM. In this case.

$$I_C = I_{IO} \bullet K \tag{8}$$

substituting Equation 1 and 8 into Equation 7 reveals:

$$I_{LO}(t) = \frac{C}{K^2} \bullet \frac{dV_{LO}}{dt}$$
 (9)

The equation in terms of the LO-side has yielded a K² scaling factor for C, specified in the denominator of the equation.

A K factor less than unity results in an effectively larger capacitance on the low-voltage side when expressed in terms of the high-voltage side. With K = 1/16 as shown in Figure 21, C = 1μ F would appear as C = 256μ F when viewed from the low-voltage side.

Low impedance is a key requirement for powering a high-current, low-voltage load efficiently. A switching regulation stage should have minimal impedance while simultaneously providing appropriate filtering for any switched current. The use of a BCM between the regulation stage and the point-of-load provides a dual benefit of scaling down series impedance leading back to the source and scaling up shunt capacitance or energy storage as a function of its K factor squared. However, these benefits are not achieved if the series impedance of the BCM is too high. The impedance of the BCM must be low, i.e., well beyond the crossover frequency of the system.

A solution for keeping the impedance of the BCM low involves switching at a high frequency. This enables the use of small magnetic components because magnetizing currents remain low. Small magnetics mean small path lengths for turns. Use of low-loss core material at high frequencies also reduces core losses.

The two main terms of power loss in the BCM module are:

- No-load power dissipation (P_{HL,NL}): defined as the power used to power up the module with an enabled powertrain at no load.
- Resistive loss (P_{RLO}): refers to the power loss across the BCM module modeled as pure resistive impedance.

$$P_{DISSIPATED} = P_{HI_NL} + P_{RIO} \tag{10}$$

Therefore,

$$P_{LO_OUT} = P_{HI_IN} - P_{DISSIPATED} = P_{HI_IN} - P_{HI_NL} - P_{R_{IO}}$$
 (11)

The above relations can be combined to calculate the overall module efficiency:

$$\eta = \frac{P_{LO_OUT}}{P_{HI_IN}} = \frac{P_{HI_IN} - P_{HI_IN} - P_{R_{LO}}}{P_{HI_IN}}$$
(12)

$$= \ \frac{V_{\scriptscriptstyle HI} \bullet I_{\scriptscriptstyle HI} - P_{\scriptscriptstyle HI_NL} - (I_{\scriptscriptstyle LO})^2 \bullet R_{\scriptscriptstyle LO}}{V_{\scriptscriptstyle HI} \bullet I_{\scriptscriptstyle HI}}$$

$$= 1 - \left(\frac{P_{HI_NL} + (I_{LO})^2 \cdot R_{LO}}{V_{HI} \cdot I_{HI}}\right)$$

Thermal Considerations

The VIA package provides effective conduction cooling from either of the two module surfaces. Heat may be removed from the pin-side surface, the non-pin-side surface or both. The extent to which these two surfaces are cooled is a key component for determining the maximum power that can be processed by a BCM, as can be seen from the specified thermal operating area in Figure 1. Since the BCM has a maximum internal temperature rating, it is necessary to estimate this temperature based on a system-level thermal solution. For this purpose, it is helpful to simplify the thermal solution into a roughly equivalent circuit where power dissipation is modeled as a current source, isothermal surface temperatures are represented as voltage sources and the thermal resistances are represented as resistors. Figure 22 shows the "thermal circuit" for the BCM in a VIA package.




Figure 22 — Double-sided cooling thermal model

In this case, the internal power dissipation is P_{DISS} , $\theta_{INT_PIN_SIDE}$ and $\theta_{INT_NON_PIN_SIDE}$ are the thermal resistance characteristics of the BCM and the pin-side and non-pin-side surface temperatures are represented as $T_{C_PIN_SIDE}$ and $T_{C_NON_PIN_SIDE}$. It is interesting to note that the package itself provides a high degree of thermal coupling between the pin-side and non-pin-side case surfaces (represented in the model by the resistor θ_{HOU}). This feature enables two main options regarding thermal designs:

Single-side cooling: the model of Figure 22 can be simplified by calculating the parallel resistor network and using one simple thermal resistance number and the internal power dissipation curves; an example for non-pin-side cooling only is shown in Figure 23.

In this case, θ_{INT} can be derived as follows:

$$\theta_{INT} = \frac{\left(\theta_{INT_PIN_SIDE} + \theta_{HOU}\right) \bullet \theta_{INT_NON_PIN_SIDE}}{\theta_{INT_PIN_SIDE} + \theta_{HOU} + \theta_{INT_NON_PIN_SIDE}}$$
(13)




Figure 23 — Single-sided cooling thermal model

■ Double-side cooling: while this option might bring limited advantage to the module internal components (given the surface-to-surface coupling provided), it might be appealing in cases where the external thermal system requires allocating power to two different elements, such as heat sinks with independent airflows or a combination of chassis/air cooling.

Current Sharing

The performance of the BCM is based on efficient transfer of energy through a transformer without the need of closed loop control. For this reason, the transfer characteristic can be approximated by an ideal transformer with a positive temperature coefficient series resistance.

This type of characteristic is close to the impedance characteristic of a DC power distribution system both in dynamic (AC) behavior and for steady state (DC) operation.

When multiple BCM modules of a given part number are connected in an array, they will inherently share the load current according to the equivalent impedance divider that the system implements from the power source to the point-of-load. Ensuring equal current sharing among modules requires that BCM array impedances be matched.

Some general recommendations to achieve matched array impedances include:

- Dedicate common copper planes/wires within the PCB/Chassis to deliver and return the current to the modules.
- Provide as symmetric a PCB/Wiring layout as possible among modules

For further details see <u>AN:016 Using BCM Bus Converters in High Power Arrays.</u>




Figure 24 — BCM module array

Fuse Selection

In order to provide flexibility in configuring power systems, BCM in a VIA package modules are not internally fused. Input line fusing of BCM products is recommended at the system level to provide thermal protection in case of catastrophic failure.

The fuse shall be selected by closely matching system requirements with the following characteristics:

- Current rating (usually greater than maximum current of BCM module)
- Maximum voltage rating (usually greater than the maximum possible input voltage)
- Ambient temperature
- Nominal melting I²t
- Recommend fuse: see safety agency approvals (HI side)

Reverse Operation

BCM modules are capable of reverse power operation. Once the unit is started, energy will be transferred from the low-voltage side back to the high-voltage side whenever the low-side voltage exceeds $V_{\text{HI}} \bullet K$. The module will continue operation in this fashion as long as no faults occur.

To use the module in reverse, it must first be started from the high-voltage side. If a high-voltage source is not available for start up, see:

AN:038 HV ChiP™ BCM® Reverse Start Up Circuit

Fault protection that protects the module in forward operation also protects the module in reverse operation. The protection level scales with the K factor when changing the reference side of the module. Operation of the the module protection for UVLO changes from auto recovery to latching. The bootstrap circuit used to start from the low side must be re-engaged to restart.

Transient operation in reverse is expected in cases where there is significant energy storage on the low-voltage side and transient voltages appear on the high-voltage side. Application qualification should check transient and fault conditions to ensure no unexpected conditions.

Dielectric Withstand

The chassis of the BCM in a VIA package is required to be connected to Protective Earth when installed in the end application and must satisfy the requirements of IEC 60950-1 for Class I products.

Summary

The case is required to be connected to protective earth in the final installation.

The construction of the BCM in a VIA package can be summarized by describing it as a "Class II" component installed in a "Class I" subassembly.




Figure 25 — BCM in a ChiP[™] package before final assembly in the VIA package




Figure 26 — BCM in a VIA package after final assembly

Filtering

The BCM in a VIA package has built-in single stage EMI filtering located on the high-voltage side. The integrated EMI filtering consists of a common mode choke and differential mode capacitors. However, it does not include Y2 capacitors for common mode filtering. Y2 common mode capacitors can be added externally on the high-voltage side between +HI and PE (Case), and -HI and PE (Case) to meet certain EMI requirements. A typical test set-up block diagram for conducted emissions is shown in Figure 27.

The integrated filtering reduces the voltage ripple on the high-voltage side. External LO-side filtering can be added as needed, with ceramic capacitance used as a LO-side bypass for this purpose. BCM HI-side and LO-side voltage ranges shall not be exceeded. An internal overvoltage function prevents operation outside of the normal operating HI-side range. However, the BCM is exposed to the applied voltage even when disabled, and must withstand it. External transient protection circuitry may be required to protect the BCM from overvoltage transients imposed by a system that would exceed maximum ratings.

The source response is generally the limiting factor in the overall system response, given the wide bandwidth of the BCM. Anomalies in the response of the source will appear at the LO side of the module multiplied by its K factor.

Total load capacitance at the LO side of the BCM shall not exceed the specified maximum to ensure correct operation in start up. Due to the wide bandwidth and small LO-side impedance of the BCM, low-frequency bypass capacitance and significant energy storage may be more densely and efficiently provided by adding capacitance at the HI-side of the BCM.

At frequencies less than 500kHz, the BCM appears as an impedance of R_{LO} between the source and load. Within this frequency range, capacitance connected at the HI side appears as an effective scaled capacitance on the LO side per the relationship defined in Equation 14.

$$C_{LO} = \frac{C_{HI}}{K^2} \tag{14}$$

This enables a reduction in the size and number of capacitors used in a typical system.

The high bandwidth of the BCM can cause load changes seen on the output up to this bandwidth to appear at the input. They must be considered in any input filter design if required. This effect is seen during power transfer in either direction, however the benefit of capacitor size reduction will consistently be on the high-voltage side.





Figure 27 — Typical test set up block diagram for Conducted Emissions

System Diagram for PMBus® Interface



The controller of the BCM in a VIA package is referenced to the low-voltage-side signal ground (SGND).

The BCM in a VIA package provides the Host PMBus system with accurate telemetry monitoring and reporting, threshold and warning limits adjustment, in addition to corresponding status flags. The standalone BCM is periodically polled for status by the host PMBus. Direct communication to the BCM is enabled by a page command. For example, the page (0x00) prior to a telemetry inquiry points to the controller data and page (0x01) prior to a telemetry inquiry points to the BCM parameters.

The BCM enables the PMBus compatible host interface with an operating bus speed of up to 400kHz. The BCM follows the PMBus command structure and specification.

PMBus® Interface

Refer to "PMBus Power System Management Protocol Specification Revision 1.2, Part I and II" for complete PMBus specifications details at http://pmbus.org.

Device Address

The PMBus address (ADDR Pin) should be set to one of the predetermined 16 possible addresses shown in the table below using a resistor between the ADDR pin and SGND pin.

The BCM accepts only a fixed and persistent address and does not support SMBus address resolution protocol. At initial power-up, the BCM controller will sample the address pin voltage and will keep this address until device power is removed.

ID	Child Address	HEX	Recommended Resistor R_{ADDR} (Ω)	
1	1010 000b	50h	487	
2	1010 001b	51h	1050	
3	1010 010b	52h	1870	
4	1010 011b	53h	2800	
5	1010 100b	54h	3920	
6	1010 101b	55h	5230	
7	1010 110b	56h	6810	
8	1010 111b	57h	8870	
9	1011 000b	58h	11300	
10	1011 001b	59h	14700	
11	1011 010b	5Ah	19100	
12	1011 011b	5Bh	25500	
13	1011 100b	5Ch	35700	
14	1011 101b	5Dh	53600	
15	1011 110b 5Eh		97600	
16	1011 111b	5Fh	316000	

Reported DATA Formats

The BCM controller employs a direct data format where all reported measurements are in Volts, Amperes, Degrees Celsius, or Seconds. The host uses the following PMBus specification to interpret received values metric prefixes. Note that the COEFFICIENTS command is not supported:

$$X = \left(\frac{1}{m}\right) \cdot (Y \cdot 10^{-R} - b)$$

Where:

X, is a "real world" value in units (A, V, °C, s)

Y, is a two's complement integer received from the BCM controller m, b and R are two's complement integers defined as follows:

Command	Code	m	R	b
TON_DELAY	60h	1	3	0
READ_VIN	88h	1	1	0
READ_IIN	89h	1	3	0
READ_VOUT [e]	8Bh	1	1	0
READ_IOUT	8Ch	1	2	0
READ_TEMPERATURE_1 [f]	8Dh	1	0	0
READ_POUT	96h	1	0	0
MFR_VIN_MIN	A0h	1	0	0
MFR_VIN_MAX	A1h	1	0	0
MFR_VOUT_MIN	A4h	1	0	0
MFR_VOUT_MAX	A5h	1	0	0
MFR_IOUT_MAX	A6h	1	0	0
MFR_POUT_MAX	A7h	1	0	0
READ_K_FACTOR	D1h	65536	0	0
READ_BCM_ROUT	D4h	1	5	0

 $^{^{[}e]}$ Default READ LO-side voltage returned when BCM unit is disabled = -300V. $^{[f]}$ Default READ Temperature returned when BCM unit is disabled = -273°C.

No special formatting is required when lowering the supervisory limits and warnings.

Supported Command List

Command	Code	Function	Default Data Content	Data Bytes
PAGE	00h	Access BCM stored information	00h	1
OPERATION	01h	Turn BCM on or off	80h	1
CLEAR_FAULTS	03h	Clear all faults	N/A	None
CAPABILITY	19h	PMBus® key capabilities set by factory	20h	1
OT_FAULT_LIMIT	4Fh ^[g]	Overtemperature protection	64h	2
OT_WARN_LIMIT	51h ^[g]	Overtemperature warning	64h	2
VIN_OV_FAULT_LIMIT	55h ^[g]	High-voltage-side overvoltage protection	64h	2
VIN_OV_WARN_LIMIT	57h ^[g]	High-voltage-side overvoltage warning	64h	2
IIN_OC_FAULT_LIMIT	5Bh ^[g]	High-voltage-side overcurrent protection	64h	2
IIN_OC_WARN_LIMIT	5Dh ^[g]	High-voltage-side overcurrent warning	64h	2
TON_DELAY	60h ^[g]	Start up delay in addition to fixed delay	00h	2
STATUS_BYTE	78h	Summary of faults	00h	1
STATUS_WORD	79h	Summary of fault conditions	00h	2
STATUS_IOUT	7Bh	Overcurrent fault status	00h	1
STATUS_INPUT	7Ch	Overvoltage and undervoltage fault status	00h	1
STATUS_TEMPERATURE	7Dh	Overtemperature and undertemperature fault status	00h	1
STATUS_CML	7Eh	PMBus communication fault	00h	1
STATUS_MFR_SPECIFIC	80h	Other BCM status indicator	00h	1
READ_VIN	88h	Reads HI-side voltage	FFFFh	2
READ_IIN	89h	Reads HI-side current	FFFFh	2
READ_VOUT	8Bh	Reads LO-side voltage	FFFFh	2
READ_IOUT	8Ch	Reads LO-side current	FFFFh	2
READ_TEMPERATURE_1	8Dh	Reads internal temperature	FFFFh	2
READ_POUT	96h	Reads LO-side power	FFFFh	2
PMBUS_REVISION	98h	PMBus compatible revision	22h	1
MFR_ID	99h	BCM controller ID	"VI"	2
MFR_MODEL	9Ah	Internal controller or BCM model	Part Number	18
MFR_REVISION	9Bh	Internal controller or BCM revision	FW and HW revision	18
MFR_LOCATION	9Ch	Internal controller or BCM factory location	"AP"	2
MFR_DATE	9Dh	Internal controller or BCM manufacturing date	"YYWW"	4
MFR_SERIAL	9Eh	Internal controller or BCM serial number	Serial Number	16
MFR_VIN_MIN	A0h	Minimum rated high-side voltage	Varies per BCM	2
MFR_VIN_MAX	A1h	Maximum rated high-side voltage	Varies per BCM	2
MFR_VOUT_MIN	A4h	Minimum rated low-side voltage	Varies per BCM	2
MFR_VOUT_MAX	A5h	Maximum rated low-side voltage	Varies per BCM	2
MFR_IOUT_MAX	A6h	Maximum rated low-side current	Varies per BCM	2
MFR_POUT_MAX	A7h	Maximum rated low-side power	Varies per BCM	2
READ_K_FACTOR	D1h	Reads K factor	Varies per BCM	2
READ_BCM_ROUT	D4h	Reads low-voltage side output resistance	Varies per BCM	2
SET_ALL_THRESHOLDS	D5h ^[g]	Set supervisory warning and protection thresholds	6464646464h	6
DISABLE_FAULT	D7h ^[g]	Disable overvoltage, overcurrent or undervoltage supervisory faults	00h	2


 $^{^{[}g]}$ The BCM must be in a disabled state with $V_{HI} < V_{HI_UVLO-}$ and VDDB applied during a write message.



Command Structure Overview

Write Byte protocol:

The Host always initiates PMBus® communication with a START bit. All messages are terminated by the Host with a STOP bit. In a write message, the parent sends the child device address followed by a write bit. Once the child acknowledges, the parent proceeds with the command code and then similarly the data byte.






Figure 1 — PAGE COMMAND (00h), WRITE BYTE PROTOCOL

Read Byte protocol:

Continued next line

A Read message begins by first sending a Write Command, followed by a REPEATED START Bit and a Child address. After receiving the READ bit, the BCM controller begins transmission of the Data responding to the Command. Once the Host receives the requested Data, it terminates the message with a NACK preceding a stop condition signifying the end of a read transfer.




Figure 2 — ON_OFF_CONFIG COMMAND (02h), READ BYTE PROTOCOL

Write Word protocol:

When transmitting a word, the lowest order byte leads the highest order byte. Furthermore, when transmitting a Byte, the least significant bit (LSB) is sent last. Refer to System Management Bus (SMBus) specification version 2.0 for more details.

Note: Extended command and Packet Error Checking Protocols are not supported.




Figure 3 — TON_DELAY COMMAND (D6h)_WRITE WORD PROTOCOL

Read Word protocol:




Figure 4 — MFR_VIN_MIN COMMAND (88h)_READ WORD PROTOCOL

Write Block protocol:




Figure 5 — SET_ALL_THRESHOLDS COMMAND (D5h)_WRITE BLOCK PROTOCOL

Read Block protocol:




Figure 6 — SET_ALL_THRESHOLDS COMMAND (D5h)_READ BLOCK PROTOCOL

Write Group Command protocol:

Note that only one command per device is allowed in a group command.




Figure 7 — DISABLE_FAULT COMMAND (D7h)_WRITE

Supported Commands Transaction Type

A direct communication to the BCM controller and a simulated communication to non-PMBus® devices is enabled by a page command. Supported command access privileges with a pre-selected PAGE are defined in the following table. Deviation from this table generates a communication error in STATUS_CML register.

Command	Code		ata Byte s Type
		00h	01h
PAGE	00h	R/W	R/W
OPERATION	01h	R	R/W
CLEAR_FAULTS	03h	W	W
CAPABILITY	19h	R	
OT_FAULT_LIMIT	4Fh		R/W
OT_WARN_LIMIT	51h		R/W
VIN_OV_FAULT_LIMIT	55h		R/W
VIN_OV_WARN_LIMIT	57h		R/W
IIN_OC_FAULT_LIMIT	5Bh		R/W
IIN_OC_WARN_LIMIT	5Dh		R/W
TON_DELAY	60h		R/W
STATUS_BYTE	78h	R/W	R
STATUS_WORD	79h	R	R
STATUS_IOUT	7Bh	R	R/W
STATUS_INPUT	7Ch	R	R/W
STATUS_TEMPERATURE	7Dh	R	R/W
STATUS_CML	7Eh	R/W	
STATUS_MFR_SPECIFIC	80h	R	R/W
READ_VIN	88h		R
READ_IIN	89h	R	R
READ_VOUT	8Bh		R
READ_IOUT	8Ch	R	R
READ_TEMPERATURE_1	8Dh	R	R
READ_POUT	96h	R	R
PMBUS_REVISION	98h	R	
MFR_ID	99h	R	
MFR_MODEL	9Ah	R	R
MFR_REVISION	9Bh	R	R
MFR_LOCATION	9Ch	R	R
MFR_DATE	9Dh	R	R
MFR_SERIAL	9Eh	R	R
MFR_VIN_MIN	A0h	R	R
MFR_VIN_MAX	A1h	R	R
MFR_VOUT_MIN	A4h	R	R
MFR_VOUT_MAX	A5h	R	R
MFR_IOUT_MAX	A6h	R	R
MFR_POUT_MAX	A7h	R	R
READ_K_FACTOR	D1h		R
READ_BCM_ROUT	D4h		R
SET_ALL_THRESHOLDS	D5h		R/W
DISABLE_FAULT	D7h		R/W

Page Command (00h)


The page command data byte of 00h prior to a command call will address the BCM controller specific data and a page data byte of 01h would broadcast to the BCM. The value of the Data Byte corresponds to the pin name trailing number with the exception of 00h and FFh.

Data Byte	Description
00h	BCM controller
01h	BCM

OPERATION Command (01h)

The OPERATION command can be used to turn on and off the connected BCM.

If synchronous start up is required in the system, it is recommended to use the command from host PMBus in order to achieve simultaneous array start up.




This command accepts only two data values: 00h and 80h. If any other value is sent the command will be rejected and a CML Data error will result.

CLEAR FAULTS Command (03h)

This command clears all status bits that have been previously set. Persistent or active faults are re-asserted again once cleared. All faults are latched once asserted in the BCM controller. Registered faults will not be cleared when shutting down the BCM powertrain by recycling the BCM high-side voltage or sending the OPERATION command.

CAPABILITY Command (19h)



The BCM controller returns a default value of 20h. This value indicates that the PMBus® frequency supported is up to 400kHz and that both Packet Error Checking (PEC) and SMBALERT# are not supported.

OT_FAULT_LIMIT Command (4Fh),
OT_WARN_ LIMIT Command (51h),
VIN_OV_FAULT_ LIMIT Command (55h),
VIN_OV_WARN_ LIMIT Command (57h),
IIN_OC_FAULT_ LIMIT Command (5Bh),
IIN_OC_WARN_ LIMIT Command (5Dh)

The values of these registers are set in non-volatile memory and can only be written when the BCM is disabled.

The values of the above mentioned faults and warnings are set by default to 100% of the respective BCM model supervisory limits. However, these limits can be set to a lower value. For example: In order for a limit percentage to be set to 80%, one would send a write command with a (50h) Data Word.

Any values outside the range of (00h - 64h) sent by a host will be rejected, will not override the currently stored value and will set the Unsupported Data bit in STATUS_CML.

The SET_ALL_THRESHOLDS COMMAND (D5h) combines in one block overtemperature fault and warning limits, $V_{\rm HI}$ overvoltage fault and warning limits as well as $I_{\rm LO}$ overcurrent fault and warning limits. A delay prior to a read command of up to 200ms following a write of new value is required.

The VIN_UV_WARN_LIMIT (58h) and VIN_UV_FAULT_LIMIT (59h) are set by the factory and cannot be changed by the host. However, a host can disable the undervoltage setting using the DISABLE FAULT COMMAND (D7h).

All FAULT_RESPONSE commands are unsupported. The BCM powertrain supervisory limits and powertrain protection will behave as described in the Electrical Specifications. In general, once a fault is detected, the BCM powertrain will shut down and attempt to auto-restart after a predetermined delay.

TON_DELAY Command (60h)

The value of this register word is set in non-volatile memory and can only be written when the BCM is disabled.


The maximum possible delay is 100ms. Default value is set to (00h). The reported value can be interpreted using the following equation.

$$TON_DELAY_{ACTUAL} = t_{REPORTED} \cdot 10^{-3} (s)$$

Staggering start up in an array is possible with the TON_DELAY Command. This delay will be in addition to any start up delay inherent in the BCM module. For example: start up delay from application of $V_{\rm HI}$ is typically 20ms. When TON_DELAY is greater than zero, the set delay will be added to it.



STATUS BYTE (78h) and STATUS WORD (79h)



All fault or warning flags, if set, will remain asserted until cleared by the host or once the BCM and VDDB power is removed. This includes undervoltage fault, overvoltage fault, overvoltage warning, overcurrent warning, overtemperature fault, overtemperature warning, undertemperature fault, reverse operation, communication faults and analog controller shut-down fault.

Asserted status bits in all status registers, with the exception of STATUS_WORD and STATUS_BYTE, can be individually cleared. This is done by sending a data byte with one in the bit position corresponding to the intended warning or fault to be cleared. Refer to the PMBus® Power System Management Protocol Specification – Part II – Revision 1.2 for details.

The POWER_GOOD# bit reflects the state of the device and does not reflect the state of the POWER_GOOD# signal limits. The POWER_GOOD_ON COMMAND (5Eh) and POWER_GOOD_OFF COMMAND (5Fh) are not supported. The POWER_GOOD# bit is set, when the BCM is not in the active state, to indicate that the powertrain is inactive and not switching. The POWER_GOOD# bit is cleared, when the BCM is in the active state, 5ms after the powertrain is activated allowing for soft start to elapse. POWER_GOOD# and OFF bits cannot be cleared as they always reflect the current state of the device.


The Busy bit can be cleared using CLEAR_ALL Command (03h) or by writing either data value (40h, 80h) to PAGE (00h) using the STATUS_BYTE (78h).

Fault reporting, such as SMBALERT# signal output, and host notification by temporarily acquiring bus parent status is not supported.

If the BCM controller is powered through VDDB, it will retain the last telemetry data and this information will be available to the user via a PMBus Status request. This is in agreement with the PMBus standard, which requires that status bits remain set until specifically cleared. Note that in the case where the BCM $V_{\rm HI}$ is lost, the status will always indicate an undervoltage fault, in addition to any other fault that occurred.

NONE OF THE ABOVE bit will be asserted if either the STATUS_MFR_SPECIFIC (80h) or the High Byte of the STATUS WORD is set.

STATUS IOUT (7Bh)



Unsupported bits are indicated above. A one indicates a fault.




STATUS INPUT (7Ch)

VIN_OV_FAULT VIN_OV_WARNING Not Supported: VIN_UV_WARNING VIN_UV_FAULT Not Supported: Unit Off For Insufficient Input Voltage Not Supported: IIN_OC_FAULT Not Supported: IIN_OC_WARNING Not Supported: PIN_OP_WARNING


Unsupported bits are indicated above. A one indicates a fault.

STATUS TEMPERATURE (7Dh)




Unsupported bits are indicated above. A one indicates a fault.

STATUS CML (7Eh)



Unsupported bits are indicated above. A one indicates a fault. The STATUS_CML data byte will be asserted when an unsupported PMBus® command or data or other communication fault occurs.


STATUS MFR SPECIFIC (80h)



The reverse operation bit, if asserted, indicates that the BCM is processing current in reverse. Reverse current reported value is not supported.

The BCM has hardware protections and supervisory limits. The hardware protections provide an additional layer of protection and have the fastest response time. The Hardware Protections Shut-Down Fault, when asserted, indicates that at least one of the powertrain protection faults is triggered. This fault will also be asserted if a disabled fault event occurs after asserting any bit using the DISABLE_FAULTS COMMAND.

The BCM communicates with its internal secondary microcontroller via UART communication. If the BCM UART CML is asserted, it may indicate a hardware or connection issue between the BCM and the secondary microcontroller.



When the PAGE COMMAND (00h) data byte is equal to (00h), the BCM Reverse operation, Analog Controller Shut-Down Fault, and BCM UART CML bit will return the result of the active BCM. The BCM UART CML will also be asserted if the active BCM stops responding. The BCM must communicate at least once to the internal controller in order to trigger this FAULT. The BCM UART CML can be cleared using the PAGE (00h) CLEAR_FAULTS (03h) Command.



READ_VIN Command (88h)

If PAGE data byte is equal to (01h), command will return the BCM's HI-side voltage in the following format:

$$V_{HIACTUAL} = V_{HIREPORTED} \cdot 10^{-1} (V)$$

READ_IIN Command (89h)

If PAGE data byte is equal to (01h), command will return the BCM's

$$I_{HI_ACTUAL} = I_{HI_REPORTED} \bullet 10^{-3} (A)$$

HI-side current in the following format:

If PAGE data byte is equal (00h), command will also return the BCM's HI-side current.

READ_VOUT Command (8Bh)

$$V_{LO\ ACTUAL} = V_{LO\ REPORTED} \cdot 10^{-1} (V)$$

If PAGE data byte is equal to (01h), command will return the BCM's LO-side voltage in the following format:

READ_IOUT Command (8Ch)

$$I_{LO_ACTUAL} = I_{LO_REPORTED} \bullet 10^{-2} (A)$$

If PAGE data byte is equal to (01h), command will return the BCM's LO-side current in the following format:

If PAGE data byte is equal (00h), command will also return the BCM's LO-side current.

READ TEMPERATURE 1 Command (8Dh)

$$T_{ACTUAL} = \pm T_{REPORTED}$$
 (°C)

If PAGE data byte is equal to (01h), command will return the BCM's temperature in the following format:

If PAGE data byte is equal (00h), command will also return the BCM's temperature

READ POUT Command (96h)

If PAGE data byte is equal to (01h), command will return the BCM's LO-side power in the following format:

$$P_{LO\ ACTUAL} = P_{LO\ REPORTED}(W)$$

If PAGE data byte is equal to (00h), command will also return the BCM's LO-side power.

MFR_VIN_MIN Command (A0h), MFR_VIN_MAX Command (A1h), MFR_VOUT_MIN Command (A4h), MFR_VOUT_MAX Command (A5h), MFR_IOUT_MAX Command (A6h), MFR_POUT_MAX Command (A7h)

These values are set by the factory and indicate the device HI-side/LO-side voltage and LO-side current range and LO-side power capacity.

If the PAGE data byte is equal to (00h – 01h), commands report the rated BCM HI-side voltage minimum and maximum in Volts, LO-side voltage minimum and maximum in Volts, LO-side current maximum in Amperes and LO-side power maximum in Watts.

READ_K_FACTOR Command (D1h)

If PAGE data byte is equal to (01h), command will return the BCM's K factor in the following format:

$$K_FACTOR_{ACTUAL} = K_FACTOR_{REPORTED} \cdot 2^{-16}(V/V)$$


The K factor is defined in the BCM to represent the ratio of the transformer winding and hence is equal to $V_{1.0}$ / V_{HI} .

READ_BCM_ROUT Command (D4h)

If PAGE data byte is equal to (01h), command will return the BCM's LO-side resistance in the following format:

$$BCM_R_{LO\ ACTUAL} = BCM_R_{LO\ REPORTED} \bullet 10^{-5}(\Omega)$$

SET ALL THRESHOLDS Command (D5h)




The values of this register block are set in non-volatile memory and can only be written when the BCM is disabled.

This command provides a convenient way to configure all of the limits, or any combination of limits described previously using one command

 V_{HI} overvoltage, overcurrent and overtemperature values are all set to 100% of the specified supervisory limits by default and can only be set to a lower percentage.

To leave a particular threshold unchanged, set the corresponding threshold data byte to a value greater than (64h).

DISABLE FAULT Command (D7h)



Unsupported bits are indicated above. A one indicates that the supervisory fault associated with the asserted bit is disabled.

The values of this register block are set in non-volatile memory and can only be written when the BCM is disabled.

This command allows the host to disable the supervisory faults and respective statuses. It does not disable the powertrain analog protections or warnings with respect to the set limits in the SET_ALL_THRESHOLDS Command.

The HI-side undervoltage can only be disabled to a pre-set low limit as specified in the Monitored Telemetry Functional Reporting Range.

The BCM Controller Implementation vs. PMBus® Specification Rev 1.2

The BCM controller is an I²C™ compliant, SMBus compatible device and PMBus command compliant device. This section denotes some deviation, perceived as differences from the PMBus Part I and Part II specification Rev 1.2.

1. The PMBus interface meets all Part I and II PMBus specification requirements with the following differences to the transport requirement.

Un	Unmet DC parameter Implementation vs SMBus spec											
Symbol	Parameter		PMBus Interface		SMBus Rev 2.0							
		Min	Max	Min	Max							
V _{IL} [a]	Input Low Voltage	_	0.99	_	0.8	V						
V _{IH} [a]	Input High Voltage	2.31	_	2.1	V_{VDD_IN}	V						
I _{LEAK_PIN} [b]	Input Leakage per Pin	10	22	_	±5	μΑ						

[[]a] $V_{VDD_{IN}} = 3.3V$

- The BCM accepts 38 PMBus command codes. Implemented commands execute functions as described in the PMBus specification.
 - Deviations from the PMBus specification:
 - a. Section 15, fault related commands
 - The limits and Warnings unit is implemented as a percentage (%) a range from decimal (0 – 100) of the factory set limits.

- **3.** The unsupported PMBus command code response as described in the Fault Management and Reporting:
 - Deviations from the PMBus specification:
 - a. PMBus section 10.2.5.3, exceptions
 - The busy bit of the STATUS_BYTE as implemented can be cleared (80h). In order to maintain compatibility with the specification, (40h) can also be used.
 - Manufacturer Implementation of the PMBus Spec:
 - **a.** PMBus section 10.5, setting the response to a detected fault condition
 - All powertrain responses are pre-set and cannot be changed.
 - **b.** PMBus section 10.6, reporting faults and warnings to the Host
 - SMBALERT# signal and Direct PMBus Device to Host Communication are not supported. However, the PMBus interface will set the corresponding fault status bits and will wait for the host to poll.
 - c. PMBus section 10.7, clearing a shut down due to a fault
 - There is no RESET pin or EN pin in the BCM. Cycling power to the BCM will not clear a BCM Shut Down. The BCM will clear itself once the fault condition is removed.
 - **d.** PMBus Section 10.8.1, corrupted data transmission faults:
 - Packet error checking is not supported.

Data Transmission Faults Implementation

This section describes data transmission faults as implemented in the BCM controller.

		Respons	e to Host	STATUS_BYTE	STAT	US_CML	
Section	Description	NAK	FFh	CML	Other Fault	Unsupported Data	Notes
10.8.1	Corrupted data						No response; PEC not supported
10.8.2	Sending too few bits			X	X		
10.8.3	Reading too few bits			X	X		
10.8.4	Host sends or reads too few bytes			X	X		
10.8.5	Host sends too many bytes	Х		X		X	
10.8.6	Reading too many bytes		X	X	X		
10.8.7	Device busy	X	X				Device will ACK own address BUSY bit in STATUS_BYTE even if STATUS_WORD is set

 $[[]b] V_{BUS} = 5V$


Data Content Faults Implementation

This section describes data content fault as implemented in the BCM controller.


Section	Description	Response to Host	STATUS_BYTE	STATUS_CML		Notes	
Section	Description	NAK	CML	Other Fault	Unsupported Command	Unsupported Data	Notes
10.9.1	Improperly set read bit in the address byte	X	X	X			
10.9.2	Unsupported command code	X	X		X		
10.9.3	Invalid or unsupported data		X			X	
10.9.4	Data out of range		X			X	
10.9.5	Reserved bits						No response; not a fault




BCM in VIA Package Chassis (Lug) Mount Package Mechanical Drawing




BCM in VIA Package PCB (Board) Mount Package Mechanical Drawing



BCM in VIA Package PCB (Board) Mount Package Recommended Hole Pattern



4414 UHV VIA BCM TIM PAD Mechanical Drawing



In chassis-mount applications or in board-mount applications with heat sink, an insulation layer of Gap Pad TIM (for example, Henkel Bergquist Gap Pad 5000S35 thickness 20 thousands, or similar) is necessary to meet the creepage requirements from the high-voltage terminals to the case. Vicor part number 45766 is the TIM Pad recommended for use with Vicor UHV BCM4414 VIA.



Revision History

Revision	Date	Description	Page Number(s)
1.0	04/18/19	Initial release	n/a
1.1	08/06/20	Updated terminology	25, 27, 28, 29, 32
1.2	10/26/20	Updated to include reverse-direction operation options and specifications	5, 9, 23, 24

Note: page added in Rev 1.7.



Vicor's comprehensive line of power solutions includes high density AC-DC and DC-DC modules and accessory components, fully configurable AC-DC and DC-DC power supplies, and complete custom power systems.

Information furnished by Vicor is believed to be accurate and reliable. However, no responsibility is assumed by Vicor for its use. Vicor makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication. Vicor reserves the right to make changes to any products, specifications, and product descriptions at any time without notice. Information published by Vicor has been checked and is believed to be accurate at the time it was printed; however, Vicor assumes no responsibility for inaccuracies. Testing and other quality controls are used to the extent Vicor deems necessary to support Vicor's product warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

Specifications are subject to change without notice.

Visit http://www.vicorpower.com/dc-dc/isolated-fixed-ratio/hv-bus-converter-module for the latest product information.

Vicor's Standard Terms and Conditions and Product Warranty

All sales are subject to Vicor's Standard Terms and Conditions of Sale, and Product Warranty which are available on Vicor's webpage (http://www.vicorpower.com/termsconditionswarranty) or upon request.

Life Support Policy

VICOR'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS PRIOR WRITTEN APPROVAL OF THE CHIEF EXECUTIVE OFFICER AND GENERAL COUNSEL OF VICOR CORPORATION. As used herein, life support devices or systems are devices which (a) are intended for surgical implant into the body, or (b) support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in a significant injury to the user. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system or to affect its safety or effectiveness. Per Vicor Terms and Conditions of Sale, the user of Vicor products and components in life support applications assumes all risks of such use and indemnifies Vicor against all liability and damages.

Intellectual Property Notice

Vicor and its subsidiaries own Intellectual Property (including issued U.S. and Foreign Patents and pending patent applications) relating to the products described in this data sheet. No license, whether express, implied, or arising by estoppel or otherwise, to any intellectual property rights is granted by this document. Interested parties should contact Vicor's Intellectual Property Department.

The products described on this data sheet are protected by the following U.S. Patents Numbers: 7,145,786; 6,930,893; 10,398,040 and other patents pending.

Contact Us: http://www.vicorpower.com/contact-us

Vicor Corporation

25 Frontage Road Andover, MA, USA 01810 Tel: 800-735-6200 Fax: 978-475-6715 www.vicorpower.com

Customer Service: customer Service: customer@vicorpower.com Technical Support: apps@vicorpower.com

©2019 - 2020 Vicor Corporation. All rights reserved. The Vicor name is a registered trademark of Vicor Corporation. PMBus® is a registered trademark of SMIF, Inc. I²C™ is a trademark of NXP Semiconductor All other trademarks, product names, logos and brands are property of their respective owners.